


## FSS2306

SOT-23-3L 場效應晶體管(SOT-23-3L Field Effect Transistors)



**N-Channel Enhancement-Mode MOS FETs**

**N 沟道增强型 MOS 场效应管**

■ **MAXIMUM RATINGS 最大額定值**

Characteristic 特性參數	Symbol 符號	Max 最大值	Unit 單位
Drain-Source Voltage 漏極-源極電壓	$BV_{DSS}$	20	V
Gate- Source Voltage 柵極-源極電壓	$V_{GS}$	$\pm 12$	V
Drain Current (continuous)漏極電流-連續	$I_D$	5	A
Drain Current (pulsed)漏極電流-脈沖	$I_{DM}$	20	A
Total Device Dissipation 總耗散功率 $T_A=25^\circ\text{C}$ 環境溫度為 $25^\circ\text{C}$	$P_D$	1300	mW
Junction 結溫	$T_J$	150	$^\circ\text{C}$
Storage Temperature 儲存溫度	$T_{stg}$	-55to+150	$^\circ\text{C}$

■ **DEVICE MARKING 打標**

**FSS2306=A6SHB**



## FSS2306

### ■ ELECTRICAL CHARACTERISTICS 電特性

( $T_A=25^{\circ}\text{C}$  unless otherwise noted 如無特殊說明, 溫度為  $25^{\circ}\text{C}$ )


Characteristic 特性參數	Symbol 符號	Min 最小值	Typ 典型值	Max 最大值	Unit 單位
Drain-Source Breakdown Voltage 漏極-源極擊穿電壓( $I_D=250\mu\text{A}, V_{GS}=0\text{V}$ )	$BV_{DSS}$	20	23	—	V
Gate Threshold Voltage 柵極開啓電壓( $I_D=250\mu\text{A}, V_{GS}=V_{DS}$ )	$V_{GS(th)}$	0.5	0.8	1.5	V
Diode Forward Voltage Drop 內附二極管正向壓降( $I_S=1.25\text{A}, V_{GS}=0\text{V}$ )	$V_{SD}$	—	—	1.2	V
Zero Gate Voltage Drain Current 零柵壓漏極電流( $V_{GS}=0\text{V}, V_{DS}=30\text{V}$ ) ( $V_{GS}=0\text{V}, V_{DS}=24\text{V}, T_A=55^{\circ}\text{C}$ )	$I_{DSS}$	—	—	1 10	$\mu\text{A}$
Gate Body Leakage 柵極漏電流( $V_{GS}=\pm 12\text{V}, V_{DS}=0\text{V}$ )	$I_{GSS}$	—	—	$\pm 100$	nA
Static Drain-Source On-State Resistance 靜態漏源導通電阻( $I_D=5\text{A}, V_{GS}=4.5\text{V}$ )	$R_{DS(ON)}$	—	25	35	$\text{m}\Omega$
Static Drain-Source On-State Resistance 靜態漏源導通電阻( $I_D=2.6\text{A}, V_{GS}=2.5\text{V}$ )	$R_{DS(ON)}$	—	30	45	$\text{m}\Omega$
Input Capacitance 輸入電容 ( $V_{GS}=10\text{V}, V_{DS}=15\text{V}, f=1\text{MHz}$ )	$C_{ISS}$	—	820	—	pF
Output Capacitance 輸出電容 ( $V_{GS}=10\text{V}, V_{DS}=15\text{V}, f=1\text{MHz}$ )	$C_{OSS}$	—	90	—	pF
Turn-ON Time 開啓時間 ( $V_{DS}=15\text{V}, V_{GS}=10\text{V}, R_{GEN}=6\Omega$ )	$t_{(on)}$	—	8.5	—	ns
Turn-OFF Time 關斷時間 ( $V_{DS}=15\text{V}, V_{GS}=10\text{V}, R_{GEN}=6\Omega$ )	$t_{(off)}$	—	31	—	ns

Pulse Width  $\leq 300\mu\text{s}$ ; Duty Cycle  $\leq 2.0\%$

## FSS2306

### ■ DIMENSION 外形封裝尺寸

單位(UNIT): mm



代碼	范围(单位: mm)
A	1.050~1.250
A1	0.000~0.100
A2	1.050~1.150
b	0.300~0.500
c	0.100~0.200
D	2.820~3.020
E1	1.500~1.700
E	2.650~2.950
e	0.950(BSC)
e 1	1.800~2.00
L	0.300~0.600
L1	0.600REF.
$\theta$	0°~8°