


**1A SURFACE MOUNT SCHOTTKY BRIDGE**
**RECTIFIER Reverse Voltage - 40 to 200 V**
**Forward Current - 1A**
**FEATURES**

- ◆ High current capability
- ◆ Low forward voltage drop
- ◆ Low power loss, high efficiency
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives


**MECHANICAL DATA**

- ◆ Case: MBS
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 100mg / 0.0035oz


**MBS**
**Maximum Ratings and Electrical characteristics**

Ratings at 25 °C ambient temperature unless otherwise specified.


Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	MB14S	MB16S	MB18S	MB110S	MB120S	Units
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	40	60	80	100	200	<b>V</b>
Maximum RMS voltage	$V_{RMS}$	28	42	56	70	140	<b>V</b>
Maximum DC Blocking Voltage	$V_{DC}$	40	60	80	100	200	<b>V</b>
Average Rectified Output Current	$I_{F(AV)}$	1					<b>A</b>
Peak Forward Surge Current 8.3 ms Single Half Sine-Wave Superimposed on Rated Load(JEDEC method)	$I_{FSM}$	40		30			<b>A</b>
Max Instantaneous Forward Voltage at 1 A	$V_F$	0.55	0.70	0.85	0.90		<b>V</b>
Maximum DC Reverse Current @ $T_A=25^\circ C$ at Rated DC Blocking Voltage @ $T_A=100^\circ C$	$I_R$	0.3 10		0.2 5	0.1 2		$\mu A$
Typical Junction Capacitance <sup>(Note1)</sup>	$C_J$	110		80			$pF$
Typical Thermal Resistance <sup>(Note2)</sup>	$R_{\theta JA}$			100			$^\circ C/W$
Operating and Storage Temperature Range	$T_j$			-55 ~ +125			$^\circ C$
Storage Temperature Range	$T_{stg}$			-55 ~ +150			$^\circ C$



(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(2) Mounted on glass epoxy PC board with 4×1.5"×1.5" (3.81×3.81 cm) copper pad.




**Fig.1 Forward Current Derating Curve**



**Fig.2 Typical Reverse Characteristics**




**Fig.4 Typical Junction Capacitance**



### Package Outline


**MBS**

Plastic surface mounted package; 4leads



UNIT		A	C	D	E	H <sub>E</sub>	d	e	L	L <sub>1</sub>	a	<
mm	max	2.6	0.22	5.0	4.1	7.0	2.7	0.7	1.7	1.1	0.2	7°
	min	2.2	0.15	4.5	3.6	6.4	2.3	0.5	1.3	0.5	—	
mil	max	102	8.7	197	161	276	106	28	67	43	8	7°
	min	94	5.9	177	142	252	91	20	51	20	—	

#### The recommended mounting pad size



#### Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
MBS	Tape/Reel,13"reel	3000	EIA-481-1