

## OEG

## **Miniature PCB Relay SDT-R**

10A contact rating

Approvals

Tecl

- UL TV-5 and TV-8 rating
- 1 form A (NO) contact arrangement
- Sensitive and standard coils available

Typical applications Appliances, HVAC, cable TV, monitor display



### Contact Data (continued)

Technical data of approved types on request		Coil vers
		Coil
Contact Data		code
Contact arrangement	1 Form A (NO)	
Rated voltage	250VAC, 30VDC	SDT-LMI
Max. switching voltage	250VAC, 30VDC	003
Rated current	5 to 10A	005
Contact material	AgSnO <sub>2</sub>	006
Min. recommended contact load	100mA at 5VDC	009
Frequency of operation	360 ops./h	012
Operate/release time max.	15/5ms	018
Electrical endurance		024
SDT-LMR(2): 5A, 250VAC res, 70°C	100x10 <sup>3</sup> ops.	SDT-DM
TV-5, 120VAC 25x10 <sup>3</sup> ops.		003
SDT-DMR(2): 10A, 250VAC res, , 70	)°C 100x10 <sup>3</sup> ops.	005
TV-8, 120VAC 25x10 <sup>3</sup> ops.		006
Contact ratings	5 to 10A	009
Mechanical endurance, DC coil	10x10 <sup>6</sup> operations	012
	÷	018
		024

Coil Data	
Coil voltage range	3 to 48VDC
Operative range, IEC 61810	1
Coil insulation system according UL	Class E

UL E58304, TUV R50138781, VDE 40019832, CQC03001002917

Coil	Rated	Operate	Release	Coil	Rated coil	
code	voltage	voltage	voltage	resistance	power	
	VDC	VDC	VDC	Ω±10%	mW	
SDT-LM	R & SDT-DM	R2				
003	3	2.25	0.3	36	250	
005	5	3.75	0.5	100	250	
006	6	4.50	0.6	144	250	
009	9	6.75	0.9	324	250	
012	12	9.00	1.2	576	250	
018	18	13.50	1.8	1296	250	
024	24	18.00	2.4	2304	250	
SDT-DM	R					
003	3	2.25	0.3	16.7	540	
005	5	3.75	0.5	46.3	540	
006	6	4.50	0.6	66.7	540	
009	9	6.75	0.9	150	540	
012	12	9.00	1.2	267	540	
018	18	13.50	1.8	600	540	
024	24	18.00	2.4	1067	540	
048	48	36.00	4.8	4267	540	
SDT-LM	R2					
003	3	2.25	0.3	60	150	
005	5	3.75	0.5	167	150	
006	6	4.50	0.6	240	150	
009	9	6.75	0.9	540	150	
012	12	9.00	1.2	960	150	
018	18	13.50	1.8	2160	150	
024	24	18.00	2.4	3840	150	

All figures are given for coil without pre-energization, at ambient temperature +23°C

#### **Coil operative range** 180 160 to Coil Maximum Allowable Coil Operating 140 Voltage Range Voltage 120 Voltage 100 % of Supplying 80 Cool Coil 7 60 Hot Coil 5A Applied 40 Pick-Up Voltage 20 0 -40 -20 0 20 40 60 80 100 120 140 Ambient Temp. (°C)

#### Electrical endurance







#### 04-2011, Rev. 0411 www.te.com © 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.

1



## Miniature PCB Relay SDT-R (Continued)

Insulation Data	
Initial dielectric strength	
between open contacts	1000V <sub>rms</sub>
between contact and coil	4000V <sub>rms</sub>
Clearance/creepage	
between contact and coil	>1.6/3.2mm
Other Data	
Material compliance: EU RoHS/ELV,	China RoHS, REACH, Halogen content
refer to the	Product Compliance Support Center at
www.te.co	m/customersupport/rohssupportcenter
Ambient temperature	-30°C to +70°C
Category of environmental protection	1
IEC 61810	RTII - flux proof,
	RTIII - wash tight
Shock resistance (functional)	10g
Shock resistance (destructive)	100g
Weight	11g
Resistance to soldering heat THT	
IEC 60068-2-20	RTII: 270°C/10s
	RTIII: 260°C/5s
Packaging/unit	tube/25 pcs., carton box/1000 pcs.
	tray/100 pcs., carton box/1000 pcs.

#### **Terminal assignment**

Bottom view on solder pins



### PCB layout

Bottom view on solder pins



2 – .059 DIA

#### Dimensions



2

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section.

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at <a href="http://relays.te.com/definitions">http://relays.te.com/definitions</a>

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.



# Miniature PCB Relay SDT-R (Continued)

								1		ı	
Product code structure		Typical product code	SDT	-S	-1	12	D	M	R	2	,000
Basic type											
<b>SDT</b> Miniature PCB Relay SDT-R											
Enclosure											
S Snap on cover											
Number of poles											
1 1 pole											
Coil voltage											
Coil code: please refer to coil versio	ns table (e	e.a. 05=5VDC)									
Coil input		<u> </u>									
D Standard (540mW)	L	Sensitive (250mW)									
Contact arrangement								1			
M 1 form A (NO) contact											
Design									-		
R New design											
Coil type										,	
Blank Standard	2	as LMR2: 150mW c									
		as DMR2: 250mW c	coll consum	otion							
Suffix											
000 Standard											

,000 Standard

Other	types	011	request	

Product code	Coil	Coil sensitivity	Design	<b>Cont.material</b>	Arrangement	Coil type	Part number
SDT-S-105LMR,000	5VDC	Sensitive	new design	AgSnO <sub>2</sub>	1 form A (NO)	250mW	8-1419125-1
SDT-S-112LMR,000	12VDC					standard coil	9-1419125-9
SDT-S-124LMR,000	24VDC						1419126-2
SDT-S-103DMR,000	3VDC	Standard				540mW coil	1461267-1
SDT-S-105DMR,000	5VDC					standard coil	8-1419125-0
SDT-S-112DMR,000	12VDC						9-1419125-7
SDT-S-118DMR,000	18VDC						1461267-3
SDT-S-124DMR,000	24VDC						1419126-1
SDT-S-148DMR,000	48VDC						1461023-2
SDT-S-105LMR2,000	5VDC	Sensitive				150mW coil	8-1419125-3
SDT-S-109LMR2,000	9VDC						9-1419125-5
SDT-S-105DMR2,000	5VDC	Standard				250mW coil	9-1440002-6
SDT-S-109DMR2,000	9VDC						9-1440002-8

3