

M12 CAT5 Bu gerade VWM



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 381 2803
Specification	M12 CAT5 Bu gerade VWM
HARTING eCatalogue	https://b2b.harting.com/21033812803

Identification

Category	Connectors
Series	Circular connectors M12
Identification	PushPull
Element	PCB adapter
Specification	Straight incl. housing for front mounting

Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Locking type	Screw locking PushPull
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Pack contents	60 pieces in a tray

Technical characteristics

Rated current	0.5 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	$>10^8 \Omega$



Pushing Performance

Technical characteristics

Contact resistance	≤10 mΩ
Tightening torque	2 Nm Lock nut
Ambient temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 when mated
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Isolation group	IIIa (175 ≤ CTI < 400)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	IEC 61076-2-109
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	60
Net weight	25.36 g
Country of origin	Romania
European customs tariff number	85444290



Pushing Performance

Commercial data

eCl@ss

27440402 PCB connector