



RECOMMENDED P.C.B.\*LAYOUT



CIRCUIT DIAGRAM

Specifications

Rating: DC 12V/50mA  
 Contact Resistance: 500mΩ max  
 Insulation resistance: DC100V 60S 100MΩ min  
 Dielectric strength: AC250V(50~60HZ)60S min  
 Operation force: 160±30gf 180±30gf 240±50gf  
 Operating Life: 300,000cycles 100,00cycles  
 Travels: 0.13±0.05mm



LAND PATTERN PLAN

PAPT NO	TS-2630-X
Operating Force	B:160gf C:260gf
Height	H:0.65

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	KNOB	1	POLYAMIDE	BLACK
4	FILM	1	POLYAMIDE	WHITE
3	DOME	2	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	POLYAMIDE	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	TACT SWITCH
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.: TS-2630-X
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					units: mm
ΔX					tolerance: X.X ±0.2mm
ΔX					X.XX ±0.1mm
MARK					X.XXX ±0.05mm