

NOTES1:

UL Standard

1. Rated voltage/current : 300V / 20A
3. Torque value : M2.5 , 3.5Lb.in
4. Wire range : 30~12AWG

IEC Standard

1. Rated voltage/current : 450V / 24A
2. Torque value : M2.5 , 0.4N·m
3. Wire range : 0.5~2.5mm²

NOTES2:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Pitch : 7.50mm, Poles : N=02~16P
3. Stripping length : 12~13mm
4. Withstanding voltage : AC2500V/1Min
5. Operating temperature : -40°C~+105°C
6. Undimensioned tolerances:

Pitch range in mm	Nominal dimension range		mm	mm	mm	mm	mm
	Over	In					
6	10	30	60	100	150	0.1/10	0.1/10
10	24	30	60	100	150	<	<
±0.15/±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°




7. RoHS Compliance

Ordering Information

JL105R-750 XX G 0 1

Pitch 750=7.5PH No. of pins 2P~24P Housing Color B=Black G=Green U=Blue R=Red W=White Y=Yellow D=Orange E=Grey

Packing 0=Pe bag T=Tube A=Tray



REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
A0		NEW		21.08.16

DRAW	SHUANGPING ZHENG	SCALE	FIT	PART NO.	
CHECK	LICHAD LIU	UNIT	mm	JL105R-750XXG01	
APPROVE	YONGLIANG GAO	SIZE	A4	DONGGUAN JINLING ELECTRONIC CO., LTD	
		SHEET	1/1	TITLE: JL105R-7.5-XXP 螺钉式/弯脚/绿色	
		PRD			

JILIN 东莞市锦凌电子有限公司
DONGGUAN JINLING ELECTRONIC CO., LTD

PART NO. JL105R-750XXG01

TITLE: JL105R-7.5-XXP 螺钉式/弯脚/绿色