

承認書

SPECIFICATION FOR APPROVAL

CUSTOMER: 2144


DESCRIPTION: WIRE WOUND TYPE COMMON MODE FILTER

DDY PART NO: WBA1206D222PT-HF

CUSTOMER MODEL NO: _____

DRAWING		
MADE	CHECKED	APPROVED
余运鸿	曹春宁	陈启善
DATE:	2021年2月1日	

CUSTOMER APPROVE



惠州市德立电子有限公司
HUI ZHOU DE LI ELECTRONICS CO., LTD


廣東省博羅縣洲際工業園梅園三路
NO.3 MEI YUAN ROAD, ZHOU JI INDUSTRIAL AREA, BOLUO COUNTY GUANGDONG

電話：0752-6207968 0752-6207962

傳真：0752-6207969

郵編：516100

Http://ddycoils.com



惠州市德立电子有限公司

HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A1.0
DESCRIPTION:	WIRE WOUND TYPE COMMON MODE FILTER	PAGE NO:	PAGE 1 OF 6
PART NO:	WBA1206D222PT-HF	SN.	
CUSTOMER NO:		DATE:	2021年2月1日

CATALOG

Resume	P2
Shape & Dimension	P3
Characteristic	P3
Part numbering system	P3
General specification	P3
Test Data for samples	P4
Soldering Conditions	P5
Package Information	P6




惠州市德立电子有限公司

HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A1.0
DESCRIPTION:	WIRE WOUND TYPE COMMON MODE FILTER	PAGE NO:	PAGE 3 OF 6
PART NO:	WBA1206D222PT-HF	SN.	
CUSTOMER NO:		DATE:	2021年2月1日

1. SHAPE & DIMENSION



CODE	A	B	C	D1	D2	E	
DIMENSION	3.20±0.20	1.60±0.20	1.9±0.2	0.7 Typ.	0.6 Typ.	0.2±0.1	

2. ELECTRICAL CHARACTERISTICS @25°C

Part Number	Z	Freq	Rdc	Irms	Rated Voltage	Min Insulation Resistance
	(Ω)	(MHz)	(Ω)max	(mA)max	Volts	MΩ
WBA1206D222PT-HF	2200	100	1.2	200	50	10

3. PART NUMBERING SYSTEM


WBA □□□□ □ □□□ □ □ — □□
 1 2 3 4 5 6 — 7

- 1 PRODUCT SYMBOL (产品代号)
- 2 DIMENSIONS (规格尺寸)
- 3 MATERIAL (芯片类型)
- 4 IMPEDANCE (阻抗)
- 5 TOLERANCE (公差) : P±25%; N±30%
- 6 PACKAGING (包装方式) : T-编带盘装; B-散装
- 7 E.P. (环保) : LF—Lead Free HF—Halogen Free FP—Red Phosphor Free

4. GENERAL SPECIFICATION

a. Rating DC current: Temperature rise(ΔT) is 40°C approximately at Irms.

APPROVED BY	CHECKED BY	DRAFT
陈启善	曹春宁	余运鸿



惠州市德立电子有限公司


HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A1.0
DESCRIPTION:	WIRE WOUND TYPE COMMON MODE FILTER	PAGE NO:	PAGE 4 OF 6
PART NO:	WBA1206D222PT-HF	SN.	
CUSTOMER NO:		DATE:	2021年2月1日

5. TEST DATA FOR SAMPLES

TEST ITEM	Z	Rdc	A	B	C	D1	D2
	(Ω)	(Ω)	(mm)	(mm)	(mm)	(mm)	(mm)
CON.	100MHz/0.5V	At 25°C	3.20±0.20	1.60±0.20	1.9±0.2	0.7 Typ.	0.6 Typ.
SPEC.	2200±25%	1.20 MAX					
1	2216.00	0.92	3.23	1.62	1.92	0.61	0.61
2	2231.00	0.91	3.21	1.62	1.90	0.63	0.61
3	2225.00	0.92	3.23	1.64	1.91	0.62	0.59
4	2229.00	0.92	3.23	1.60	1.92	0.62	0.61
5	2235.00	0.91	3.25	1.61	1.90	0.63	0.62
6	2316.00	0.92	3.21	1.61	1.93	0.62	0.61
7	2291.00	0.92	3.23	1.62	1.94	0.62	0.63
8	2291.00	0.92	3.24	1.62	1.93	0.61	0.62
9	2211.00	0.92	3.23	1.60	1.92	0.63	0.6
10	2164.00	0.92	3.23	1.63	1.93	0.64	0.61
X	2240.90	0.92	3.23	1.62	1.92	0.62	0.61
R	152.00	0.01	0.04	0.04	0.04	0.03	0.04

图示:




APPROVED BY	CHECKED BY	DRAFT
陈启善	曹春宁	余运鸿



CUSTOMER:	2144	REV NO:	A1.0
DESCRIPTION:	WIRE WOUND TYPE COMMON MODE FILTER	PAGE NO:	PAGE 5 OF 6
PART NO:	WBA1206D222PT-HF	SN.	
CUSTOMER NO:		DATE:	2021年2月1日

6. SOLDERING CONDITIONS


**Figure 1.
Re-flow
Soldering (Lead
Free)**



Note:

- Preheat circuit and products to 150°C
- 260°C tip temperature (max)
- Reflow times: no more than 2 times
- Solder paste thickness: the best 0.08mm is ,but max is 0.1mm


**Figure 2.
Wave Soldering**



Note :

- Never contact the ceramic with the iron tip
- 1.0mm tip diameter (max)


**Figure 3.
Hand Soldering**



Note:

- Use a 20 watt soldering iron with tip diameter of 1.0mm
- Limit soldering time to 3 sec.

APPROVED BY	CHECKED BY	DRAWN BY
陈启善	曹春宁	余运鸿



惠州市德立电子有限公司


HUIZHOU DELI ELECTRONICS CO., LTD

CUSTOMER:	2144	REV NO:	A1.0
DESCRIPTION:	WIRE WOUND TYPE COMMON MODE FILTER	PAGE NO:	PAGE 6 OF 6
PART NO:	WBA1206D222PT-HF	SN.	
CUSTOMER NO:		DATE:	2021年2月1日

7. PACKAGING(unit: mm)


Type	0603	0805	1206	1812
Quantity	2000	2000	2000	500

TAPING DRAWINGS




REEL DIMENSIONS(UNIT:mm)


	A	B	C	N	G
CF-8	178±2.0	22±2.0	12.5±1.5	57±2.0	8
CF-12	178±2.0	22±2.0	12.5±1.5	98±2.0	12



LEADER AND BLANK PORTION



PEELLING OFF FORCE:0.05 to 0.7N in the direction show below.



APPROVED BY	CHECKED BY	DRAFT
陈启善	曹春宁	余运鸿