



RoHS
COMPLIANT



Surface Mount General Purpose Silicon Rectifiers

Reverse Voltage - 50 to 1000 V

Forward Current - 1 A

FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Ideal for automated placement
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg / 0.00053oz

Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View

Marking Code : A1-A7

Simplified outline SOD-123FL and symbol






Parameter	Symbols	A1	A2	A3	A4	A5	A6	A7	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current at T _c = 125 °C	I _{F(AV)}	1						A	
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I _{FSM}	30						A	
Maximum Instantaneous Forward Voltage at 1 A	V _F	1.1						V	
Maximum DC Reverse Current T _a = 25 °C at Rated DC Blocking Voltage T _a = 125 °C	I _R	5 50						μA	
Typical Junction Capacitance ⁽¹⁾	C _j	8(TYP.)						pF	
Typical Thermal Resistance ⁽²⁾	R _{θJA}	90						°C/W	
Operating and Storage Temperature Range	T _j , T _{stg}	-55 ~ +150						°C	

(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



**RoHS
COMPLIANT**






RoHS
COMPLIANT



PACKAGE OUTLINE


Plastic surface mounted package; 2 leads

SOD-123FL



UNIT		A	C	D	E	e	g	H_E	<
mm	max	1.15	0.20	2.9	1.9	1.2	0.9	3.8	5°
	min	0.95	0.12	2.6	1.7	0.9	0.7	3.5	
mil	max	45	7.9	114	75	47	35	150	5°
	min	37	4.7	102	67	35	28	138	

The recommended mounting pad size



Marking

Type number	Marking code
1N4001W	A1
1N4002W	A2
1N4003W	A3
1N4004W	A4
1N4005W	A5
1N4006W	A6
1N4007W	A7