

**SMD3068 Crystal Resonator**

**7Z032768NW2**

1. Scope:

- 1.1 This specification applies to the RoHS compliance quartz crystal unit with a frequency of 32.768KHz which will be used in crystal oscillator applications.



2. Construction:

- 2.1 Type of Quartz Resonator: SMD3068


3. Electrical Characteristics

3.1 Mode of Vibration :	NT
3.2 Nominal frequency(F):	32.768KHz
3.3 Load Capacitance(C <sub>L</sub> ):	12.5PF
3.4 Frequency Tolerance at 25℃	±20ppm
3.5 Frequency Temperature Stability:	-0.034±0.006 * 10 <sup>-6</sup> /℃ <sup>2</sup> Max
3.6 Series Resistance(R <sub>r</sub> ):	65 KΩ Max
3.7 Quality Factor(Q):	60K TYP
3.8 Turnover Temperature(T <sub>o</sub> ):	25℃ ± 5℃
3.9 Operation Temperature:	-20℃ ~ +70℃
3.10 Preservation Temperature:	-55℃ ~ +125℃
3.11 Shunt Capacitance(C <sub>0</sub> ):	1.0pF Max
3.12 Motional Capacitance(C <sub>1</sub> ):	3.0fF Max
3.13 Insulation Resistance:	500MΩ at DC 100V±10V
3.14 Drive Level:	0.5μW Max

# Reliability Specification

	Item	Condition	Standard
1.	Drop characteristics	Free drop from 75cm height on a hard wooden board for 3 times. (Board is thickness more than 30 mm.)	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
2.	Mechanical shock	Device are shocked to half sine wave (1000g) three mutually perpendicular axes each 3 times	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
3.	Shake characteristics	Shake frequency 10~55Hz, cyc1~2 minutes, swing 1.5mm, direction x/y/z, all 30 minutes, test after 1 hours.	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
4.	Humidity characteristics	$+85 \pm 2^\circ\text{C}$ & 90%~95% R.H. 1000 hours	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
5.	Low temperature characteristics	$-40 \pm 2^\circ\text{C}$ , 1000 hours, put in room temperature, test after 1 hours.	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
6.	High temperature characteristics	$+125 \pm 2^\circ\text{C}$ , 1000 hours, put in room temperature, test after 1 hours.	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
7.	Temperature cycling	$-55 \pm 2^\circ\text{C}/30 \pm 3\text{min} \sim +125 \pm 2^\circ\text{C}/30 \pm 3\text{min}$ , 100 cycles	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification
8.	Refluence examination	<p>1. Max 180sec 2. Max 10 sec 3. Max 80 sec 4. Max 90 sec</p>	Frequency change: $\leq \pm 10\text{ppm}$ Rr as specification

# Package Outline Dimensions



Unit: mm

---

## Packing Specification

---

