



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:LCP

b.CONTACT:PHOSPHOR BRONZE

(SURFACE PLATING: Sn100U"~120U")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 50 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

d.OPERATING TEMPERATURE: -40°C~ +100°C

ORDERING INFORMATION

BS-16-A4AK004

电池座系列

BS-16系列

DIP 90° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK






4A-LCP WHITE

4B-LCP BLACK

工程 部

2020-05-23

LQ. HUANG



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.15mm	Sn-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.15mm	Sn-Plating
1	HOUSING	1	LCP	WHITE
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2020-05-23
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2020-05-23
X.X :±0.25	X.X :±0.5°	APVD	XueShunyang	DATE	2020-05-23
X.XX :±0.20		SCALE: 2:1	SIZE: A4	VIEW: ② ③	
X.XXX :±0.10		UNIT: mm	REV.: A/0	OBJECT: MY	
WEIGHT: 1.34g					
SHEET 1 OF 1					
		TITLE:		BS-1632-2 DIP	
		PART NO.:		BS-16-A4AK004	
		DRAW NO.:		MY-CP-0253	