

Features

- Fast switching
- Green Device Available
- Suit for 1.5V Gate Drive Applications

Application

- Notebook
- Load Switch
- Networking
- Hand-held Instruments



Package and Pin Configuration

Circuit diagram

SOT363



Top View



Absolute Maximum Ratings $T_c=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-20	V
V_{GS}	Gate-Source Voltage	± 12	V
I_D	Drain Current – Continuous ($T_c=25^\circ\text{C}$)	-1.1	A
I_{DM}	Drain Current – Pulsed ¹	-2.2	A
P_D	Power Dissipation ($T_c=25^\circ\text{C}$)	280	mW
	Power Dissipation – Derate above 25°C	2.5	$\text{mW}/^\circ\text{C}$
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction to ambient	---	350	°C/W

Electrical Characteristics ($T_J=25\text{ }^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}$, $I_D=-250\mu\text{A}$	-20	---	---	V
$\Delta BV_{DSS}/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to $25\text{ }^{\circ}\text{C}$, $I_D=-1\text{mA}$	---	-0.01	---	$\text{V}/^{\circ}\text{C}$
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-20\text{V}$, $V_{GS}=0\text{V}$, $T_J=25\text{ }^{\circ}\text{C}$	---	---	-1	μA
		$V_{DS}=-16\text{V}$, $V_{GS}=0\text{V}$, $T_J=125\text{ }^{\circ}\text{C}$	---	---	-10	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 12\text{V}$, $V_{DS}=0\text{V}$	---	---	± 20	μA

On Characteristics

$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=-4.5\text{V}$, $I_D=-0.5\text{A}$	---	400		$\text{m}\Omega$	
		$V_{GS}=-2.5\text{V}$, $I_D=-0.5\text{A}$	---	550	680		
		$V_{GS}=-1.8\text{V}$, $I_D=-0.1\text{A}$	---	750	1050		
$V_{GS(\text{th})}$	Gate Threshold Voltage		$V_{GS}=V_{DS}$, $I_D = -250\mu\text{A}$	-0.5	-0.7	1.0	V
	$\Delta V_{GS(\text{th})}$	$V_{GS(\text{th})}$ Temperature Coefficient		---	3	---	$\text{mV}/^{\circ}\text{C}$

Dynamic and switching Characteristics

Q_g	Total Gate Charge ^{2,3}	$V_{DS}=-10\text{V}$, $V_{GS}=-4.5\text{V}$, $I_D=-1\text{A}$	---	0.5		nC
Q_{gs}	Gate-Source Charge ^{2,3}		---	0.28		
Q_{gd}	Gate-Drain Charge ^{2,3}		---	0.28		
$T_{d(on)}$	Turn-On Delay Time ^{2,3}	$V_{DD}=-10\text{V}$, $V_{GS}=-4.5\text{V}$, $R_G=6\Omega$ $I_D=-1\text{A}$	---	0.4		ns
T_r	Rise Time ^{2,3}		---	0.06		
$T_{d(off)}$	Turn-Off Delay Time ^{2,3}		---	0.02		
T_f	Fall Time ^{2,3}		---	0.8		
C_{iss}	Input Capacitance	$V_{DS}=-10\text{V}$, $V_{GS}=0\text{V}$, $F=1\text{MHz}$	---	55		pF
C_{oss}	Output Capacitance		---	6		
C_{rss}	Reverse Transfer Capacitance		---	4.5		

Drain-Source Diode Characteristics and Maximum Ratings

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
V_{SD}	Diode Forward Voltage	$V_{GS}=0\text{V}$, $I_S=-0.2\text{A}$, $T_J=25\text{ }^{\circ}\text{C}$	---	-0.75	-1.1	V

Characteristic Curves




Figure 1. Output Characteristics




Figure 2. On-Resistance vs. ID




Figure 3. On-Resistance vs. VGS




Figure 4. Gate Threshold Voltage




Figure 5. Drain-Source On Resistance




Figure 6. Source-Drain Diode Forward




Figure 7. Capacitance




Figure 8. Gate Charge Characteristics




Figure 9. Power Dissipation




Figure 10. Drain Current




Figure 11. Safe Operating Area






Figure 12. R_{θJA} Transient Thermal Impedance


Outline Drawing - SOT-363(2.0X2.1)



Land Pattern - SOT-363




SOT-363 Embossed Carrier Tape



Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
SOT-363	2.25	2.55	1.20	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00


SOT-363 Tape Leader and Trailer

Package orientation in reel



Shipping: 3000pcs / Tape & Reel

SOT-363 Reel



Dimensions are in millimeter								
Reel Option	D	D1	D2	G	H	I	W1	W2
7" Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	