


## Dual N-Channel Enhancement Mode MOSFET


### Feature

	Q1	Q2
$V_{DS}$	30V	30V
ID ( $V_{GS} = 10V$ )	31A	33A
$R_{DS(ON)}$ (typ) @ $V_{GS} = 10V$	8.8 mR	7.3 mR
$R_{DS(ON)}$ (typ) @ $V_{GS} = 4.5V$	12.4 mR	10.3 mR



- 100% Avalanche Tested
- Reliable and Rugged
- Halogen- Free Devices Available

DFN3\*3-8L



Dual N-Channel MOSFET

### Applications

- Synchronous Rectifiers
- Wireless Power
- H-bridge Motor Drive

### Ordering and Marking Information

 <b>C1</b> <b>G080NH03</b> XYMXXXXXX	<b>Package Code</b> C1: DFN3*3-8L  <b>Date Code</b> XYMXXXXXX
--	---

Note: HUAYI lead-free products contain molding compounds/die attach materials and 100% matte tin plate Termination finish;which are fully compliant with RoHS. HUAYI lead-free products meet or exceed the lead-Free requirements of IPC/JEDEC J-STD-020 for MSL classification at lead-free peak reflow temperature. HUAYI defines "Green" to mean lead-free (RoHS compliant) and halogen free (Br or Cl does not exceed 900ppm by weight in homogeneous material and total of Br and Cl does not exceed 1500ppm by weight).

HUAYI reserves the right to make changes, corrections, enhancements, modifications, and improvements to this product and/or to this document at any time without notice.

## Absolute Maximum Ratings

Symbol	Parameter		MAX Q1	MAX Q2	Unit
<b>Common Ratings (T<sub>c</sub>=25°C Unless Otherwise Noted)</b>					
V <sub>DSS</sub>	Drain-Source Voltage		30		V
V <sub>GSS</sub>	Gate-Source Voltage		±20		V
T <sub>J</sub>	Maximum Junction Temperature		-55 to 175		°C
T <sub>STG</sub>	Storage Temperature Range		-55 to 175		°C
I <sub>S</sub>	Source Current-Continuous(Body Diode)	T <sub>c</sub> =25°C	31	33	A
<b>Mounted on Large Heat Sink</b>					
I <sub>DM</sub>	Pulsed Drain Current *	T <sub>c</sub> =25°C	111	118	A
I <sub>D</sub>	Continuous Drain Current	T <sub>c</sub> =25°C	31	33	A
		T <sub>c</sub> =100°C	22	23	A
P <sub>D</sub>	Maximum Power Dissipation	T <sub>c</sub> =25°C	21.4		W
		T <sub>c</sub> =100°C	10.7		W
R <sub>θJC</sub>	Thermal Resistance, Junction-to-Case		7		°C/W
R <sub>θJA</sub>	Thermal Resistance, Junction-to-Ambient **		75		°C/W
E <sub>AS</sub>	SinglePulsed-Avalanche Energy ***	L=0.1mH	22.9	34.3	mJ

Note: \* Repetitive rating; pulse width limited by max.junction temperature.

\*\* Surface mounted on 1in2 FR-4 board.

\*\*\* Limited by T<sub>jmax</sub> , starting T<sub>J</sub>=25°C, L = 0.1mH, R<sub>G</sub>= 25Ω, V<sub>GS</sub> =10V.

**Q1 Electrical Characteristics** ( $T_c = 25^\circ\text{C}$  Unless Otherwise Noted)






Symbol	Parameter	Test Conditions	Q1			Unit
			Min	Typ.	Max	
<b>Static Characteristics</b>						
$\text{BV}_{\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}, I_{\text{DS}}=250\mu\text{A}$	30	-	-	V
$I_{\text{DSS}}$	Drain-to-Source Leakage Current	$V_{\text{DS}}=30\text{V}, V_{\text{GS}}=0\text{V}$	-	-	1	$\mu\text{A}$
				$T_j=125^\circ\text{C}$	50	$\mu\text{A}$
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{DS}}=250\mu\text{A}$	1	1.6	3	V
$I_{\text{GSS}}$	Gate-Source Leakage Current	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$	-	-	$\pm 100$	nA
$R_{\text{DS}(\text{ON})^*}$	Drain-Source On-State Resistance	$V_{\text{GS}}=10\text{V}, I_{\text{DS}}= 10 \text{ A}$	-	8.8	11	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}, I_{\text{DS}}= 10\text{A}$		12.4	15	$\text{m}\Omega$
<b>Diode Characteristics</b>						
$V_{\text{SD}}^*$	Diode Forward Voltage	$I_{\text{SD}}=1\text{A}, V_{\text{GS}}=0\text{V}$	-	0.7	1.0	V
$t_{\text{rr}}$	Reverse Recovery Time	$I_{\text{SD}}=10\text{A}, dI_{\text{SD}}/dt=100\text{A}/\mu\text{s}$	-	8.2	-	ns
$Q_{\text{rr}}$	Reverse Recovery Charge		-	3.1	-	nC

**Q1 Electrical Characteristics (Cont.)** ( $T_c = 25^\circ\text{C}$  Unless Otherwise Noted)


Symbol	Parameter	Test Conditions	Q1			Unit
			Min	Typ.	Max	
<b>Dynamic Characteristics</b>						
$R_G$	Gate Resistance	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=0\text{V}, f=1\text{MHz}$	-	1.2	-	$\Omega$
$C_{\text{iss}}$	Input Capacitance	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=25\text{V}, f=1.0\text{MHz}$	-	709.1	-	$\text{pF}$
$C_{\text{oss}}$	Output Capacitance		-	87	-	
$C_{\text{rss}}$	Reverse Transfer Capacitance		-	70.7	-	
$t_{\text{d}(\text{ON})}$	Turn-on Delay Time		-	5.8	-	
$T_r$	Turn-on Rise Time	$V_{\text{DD}}=10\text{V}, R_G=2.7\Omega, I_{\text{DS}}=4\text{A}, V_{\text{GS}}=10\text{V}$	-	14.5	-	ns
$t_{\text{d}(\text{OFF})}$	Turn-off Delay Time		-	15.6	-	
$T_f$	Turn-off Fall Time		-	3.4	-	
<b>Gate Charge Characteristics</b>						
$Q_g$	Total Gate Charge ( $V_{\text{GS}}=10\text{V}$ )	$V_{\text{DS}}=15\text{V}, I_{\text{D}}=10\text{A}$		16		nC
$Q_g$	Total Gate Charge ( $V_{\text{GS}}=4.5\text{V}$ )		-	7.8	-	
$Q_{\text{gs}}$	Gate-Source Charge		-	2.9	-	
$Q_{\text{gd}}$	Gate-Drain Charge		-	3.3	-	

Note: \*Pulse test, pulse width  $\leq 300\text{us}$ , duty cycle  $\leq 2\%$

## Q1-Channel Typical Operating Characteristics


**Figure 1: Power Dissipation**

**Figure 3: Safe Operation Area**

**Figure 5: Output Characteristics**

**Figure 2: Drain Current**

**Figure 4: Thermal Transient Impedance**


Maximum Effective Transient Thermal Impedance, Junction-to-Case


**Figure 6: Drain-Source On Resistance**


## Q1-Channel Typical Operating Characteristics(Cont.)


**Figure 7: On-Resistance vs. Temperature**




**Figure 8: Source-Drain Diode Forward**



**Figure 9: Capacitance Characteristics**



**Figure 10: Gate Charge Characteristics**



**Q2 Electrical Characteristics** ( $T_c = 25^\circ\text{C}$  Unless Otherwise Noted)







Symbol	Parameter	Test Conditions	Q2			Unit
			Min	Typ.	Max	
<b>Static Characteristics</b>						
$\text{BV}_{\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}, I_{\text{DS}}=250\mu\text{A}$	30	-	-	V
$I_{\text{DSS}}$	Drain-to-Source Leakage Current	$V_{\text{DS}}=30\text{V}, V_{\text{GS}}=0\text{V}$	-	-	1	$\mu\text{A}$
				$T_j=125^\circ\text{C}$	50	$\mu\text{A}$
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{DS}}=250\mu\text{A}$	1	1.7	3	V
$I_{\text{GSS}}$	Gate-Source Leakage Current	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$	-	-	$\pm 100$	nA
$R_{\text{DS}(\text{ON})^*}$	Drain-Source On-State Resistance	$V_{\text{GS}}=10\text{V}, I_{\text{DS}}=10\text{A}$	-	7.3	9.5	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}, I_{\text{DS}}=10\text{A}$		10.3	12.5	$\text{m}\Omega$
<b>Diode Characteristics</b>						
$V_{\text{SD}}^*$	Diode Forward Voltage	$I_{\text{SD}}=1\text{A}, V_{\text{GS}}=0\text{V}$	-	0.7	1.0	V
$t_{\text{rr}}$	Reverse Recovery Time	$I_{\text{SD}}=10\text{A}, dI_{\text{SD}}/dt=100\text{A}/\mu\text{s}$	-	10	-	ns
$Q_{\text{rr}}$	Reverse Recovery Charge		-	4.4	-	nC





**Q2 Electrical Characteristics (Cont.)** ( $T_c = 25^\circ\text{C}$  Unless Otherwise Noted)

Symbol	Parameter	Test Conditions	Q2			Unit
			Min	Typ.	Max	
<b>Dynamic Characteristics</b>						
$R_G$	Gate Resistance	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=0\text{V}, f=1\text{MHz}$	-	1.0	-	$\Omega$
$C_{\text{iss}}$	Input Capacitance	$V_{\text{GS}}=0\text{V}, V_{\text{DS}}=25\text{V}, \text{Frequency}=1.0\text{MHz}$	-	966	-	$\text{pF}$
$C_{\text{oss}}$	Output Capacitance		-	117	-	
$C_{\text{rss}}$	Reverse Transfer Capacitance		-	101	-	
$t_{\text{d}(\text{ON})}$	Turn-on Delay Time		-	6.8	-	$\text{ns}$
$T_r$	Turn-on Rise Time	$V_{\text{DD}}=10\text{V}, R_G=2.7\Omega, I_{\text{DS}}=4\text{A}, V_{\text{GS}}=10\text{V}$	-	16.6	-	
$t_{\text{d}(\text{OFF})}$	Turn-off Delay Time		-	19.4	-	
$T_f$	Turn-off Fall Time		-	5.4	-	
<b>Gate Charge Characteristics</b>						
$Q_g$	Total Gate Charge ( $V_{\text{GS}}=10\text{V}$ )	$V_{\text{DS}}=15\text{V}, I_{\text{D}}=10\text{A}$		23.2		$\text{nC}$
$Q_g$	Total Gate Charge ( $V_{\text{GS}}=4.5\text{V}$ )		-	11.8	-	
$Q_{\text{gs}}$	Gate-Source Charge		-	4.0	-	
$Q_{\text{gd}}$	Gate-Drain Charge		-	5.0	-	



Note: \*Pulse test, pulse width  $\leq 300\text{us}$ , duty cycle  $\leq 2\%$

## Q2-Channel Typical Operating Characteristics



**Figure 1: Power Dissipation**

**Figure 3: Safe Operation Area**

**Figure 5: Output Characteristics**

**Figure 2: Drain Current**

**Figure 4: Thermal Transient Impedance**

**Figure 6: Drain-Source On Resistance**


**Q2-Channel Typical Operating Characteristics(Cont.)**
**Figure 7: On-Resistance vs. Temperature**

**Figure 8: Source-Drain Diode Forward**

**Figure 9: Capacitance Characteristics**

**Figure 10: Gate Charge Characteristics**




## Avalanche Test Circuit



## Switching Time Test Circuit



## Gate Charge Test Circuit




## Device Per Unit


Package Type	Unit	Quantity
DFN3*3-8L	Reel	3000

## Package Information


DFN3\*3-8L



TOP VIEW




BOTTOM VIEW



SIDE VIEW

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	0.70	0.75	0.80
A1	0.00	0.02	0.05
b	0.35	0.40	0.45
b1	0.30REF		
c	0.18	0.20	0.25
D	2.90	3.00	3.10
D2	2.30	2.40	2.50
Nd	1.90	1.95	2.00
E	2.90	3.00	3.10
E1	0.89	0.99	1.09
E2	0.42	0.52	0.62
e	0.65BSC		
K	0.35REF		
K1	0.06REF		
K2	0.25REF		
L	0.27	0.32	0.37
L1	0.10REF		
h	0.20	0.25	0.30

## Classification Profile



## Classification Reflow Profiles

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
<b>Preheat &amp; Soak</b>		
Temperature min ( $T_{smin}$ )	100 °C	150 °C
Temperature max ( $T_{smax}$ )	150 °C	200 °C
Time ( $T_{smin}$ to $T_{smax}$ ) ( $t_s$ )	60-120 seconds	60-120 seconds
Average ramp-up rate ( $T_{smax}$ to $T_p$ )	3 °C/second max.	3°C/second max.
Liquidous temperature ( $T_L$ )	183 °C	217 °C
Time at liquidous ( $t_L$ )	60-150 seconds	60-150 seconds
Peak package body Temperature ( $T_p$ )*	See Classification Temp in table 1	See Classification Temp in table 2
Time ( $t_p$ )** within 5°C of the specified classification temperature ( $T_c$ )	20** seconds	30** seconds
Average ramp-down rate ( $T_p$ to $T_{smax}$ )	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.

\*Tolerance for peak profile Temperature ( $T_p$ ) is defined as a supplier minimum and a user maximum.

\*\* Tolerance for time at peak profile temperature ( $t_p$ ) is defined as a supplier minimum and a user maximum.

# HYG080NH03LR1C1

Table 1.SnPb Eutectic Process – Classification Temperatures (Tc)

Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2.Pb-free Process – Classification Temperatures (Tc)

Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> ≥2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

## Reliability Test Program

Test item	Method	Description
SOLDERABILITY	JESD-22, B102	5 Sec, 245°C
HTRB	JESD-22, A108	168Hrs/500Hrs/1000Hrs, Bias @ 150°C
PCT	JESD-22, A102	96 Hrs, 100%RH, 2atm, 121°C
TCT	JESD-22, A104	500 Cycles, -55°C~150°C

### Customer Service

Worldwide Sales and Service: sales@hymexa.com

Technical Support: Technology@hymexa.com

Huayi Microelectronics Co., Ltd.

No.8928,Shangji Road,Economic and Technological Development Zone,Xi'an,China

TEL: (86-029) 86685706

FAX: (86-029) 86685705

E-mail: sales@hymexa.com

Web net: www.hymexa.com