



Specifications:

规格:

Voltage rating: 50V AC/DC

额定电压: 50V AC/DC

Current rating: 0.8A AC/DC

额定电流: 0.8A AC/DC

Withstanding voltage: 250V AC/minute

耐受电压: 250V AC/分钟

Temperature range: -25°C - +85°C

温度范围: -25°C - +85°C

X1004 W V S -2xXX -9T V01
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: W-WAFER
- ③ Wedding Board Angle: V-Stringht 180°
- ④ Welding way : S-SMT
- ⑤ Row No. Pin No.: 2xXX
- ⑥ Material: 9T-PA9T 94V-0
- ⑦ Plating Category: V01-Gold Flash

PIN	DIM A	DIM B	DIM C	DIM D
2X10P	9.00	12.30	10.45	11.25
2X15P	14.00	17.30	15.45	16.25
2X20P	19.00	22.30	20.45	21.25
2X25P	24.00	27.30	25.45	26.25

				DSND		DATE		SCALE: N/A	MODEL TYPE: 1.0 mm Crimp Style Connector	
				XKB	ANGLAR	±5°		VIEW:	PART NO.: X1004WVS-2xXX-9TV01	
ΔX					L ≤ 4	±0.2		UNIT: mm/in	DWG NO: X-X1004WVS-2xXX-9TV01	
ΔX					4 < L ≤ 16	±0.3		SIZE: A4		
ΔX					16 < L ≤ 63	±0.4				
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5				
REVISIONS					UNSPECIFIED TOLERANCES					
www.helloxkb.com					XKB INDUSTRIAL PRECISION CO., LIMITED					
								WEIGHT	SHEET	REVISION
								1.0g	1/1	A0