

Features

- 2 μ A Ground Current at no Load
- $\pm 2\%$ Output Accuracy
- 200mA Output Current
- Wide Operating Input Voltage Range: 2V to 36V
- Dropout Voltage: 0.65V at 100mA ($V_{OUT}=5V$)
- Support Fixed Output Voltage 1.8V, 3.3V, 5V, 9V, 12V
- Stable with Ceramic or Tantalum Capacitor
- Current Limit Protection
- Over-Temperature Protection
- SOT-23-5 Package Available

Applications

- Portable, Battery Powered Equipment
- Low Power Microcontrollers
- Laptop, Palmtops and PDAs
- Wireless Communication Equipment
- Audio/Video Equipment
- Car Navigation Systems
- Industrial Controls
- Weighting Scales
- Meters
- Home Automation

General Description

The TPMIC5233 is a low dropout (LDO) voltage regulators with enable function offering the benefits of high input voltage, low-dropout voltage, low-power consumption, and miniaturized packaging.

The features of low quiescent current as low as 2 μ A and zero disable current is ideal for powering the battery equipment to a longer service life. The TPMIC5233

is stable with the ceramic output capacitor over its wide input range from 2V to 36V and the entire range of output load current.

Ordering Information


TPMIC5233-3.3YM5

YM5:SOT23-5 Package

Output voltage: 12=1.2V
15=1.5V
18=1.8V
30=3.0V
33=3.3V
50=5.0V
A9=9V
B2=12V

Features

PIN CONFIGURATION



Pin No	Pin Name	Pin Function
1	VIN	Input of Supply Voltage.
2	GND	Ground
3	EN	Enable Control Input.
4	NC	No Internal Connection.
5	VOUT	Output of the Regulator

Typical Application Circuit





Figure 1: Application circuit of Fixed V_{OUT} LDO with enable and sense functions

BLOCK DIAGRAM



Absolute Maximum Ratings

Recommended Operating Conditions

Supply Input Voltage ----- 3.5V to 36V
Junction Temperature Range ----- -40°C to 125°C
Ambient Temperature Range----- -40°C to 85°C



TECH PUBLIC

—台舟电子—

TPMIC5233-3.3YM5

36V,200mA,2uA, Higt PSRR Voltage Reaulators

www.sot23.com.tw







Electrical Characteristics







(V_{IN}=15V, V_{EN}=5V, T_A=25°C, unless otherwise specified) (Note 1)







Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Supply Voltage	V _{IN}		2	--	36	V
DC Output Voltage Accuracy		I _{LOAD} =0.1mA	-2		2	%
Dropout Voltage (I _{LOAD} =100mA)	V _{DROP}	V _{OUT} ≥ 5V	--	0.66		V
	V _{DROP_3.3V}	V _{OUT} = 3.3V		0.75		
	V _{DROP_1.8V}	V _{OUT} = 1.8V		1		
Ground Current (I _{LOAD} = 0mA)	I _Q	V _{OUT} ≤ 5V		2		μA
	I _{QH}	5V < V _{OUT} ≤ 12V		4.5		
Shutdown Ground Current	I _{SD}	V _{EN} = 0V, V _{OUT} = 0V		0.01	0.5	μA
V _{OUT} Shutdown Leakage Current	I _{LEAK}			0.01	0.5	μA
Enable Threshold Voltage	V _{IH}	EN Rising			2	V
	V _{IL}	EN Falling	0.6			
EN Input Current	I _{EN}	V _{EN} = 36V		10	100	nA
Line Regulation	ΔLINE	I _{LOAD} =1mA, 5 ≤ V _{IN} ≤ 36V	--	0.3		%
Load Regulation	ΔLOAD	1mA≤ I _{LOAD} ≤ 0.2A		0.1		%
Output Current Limit	I _{LIM}	V _{OUT} =0	200	300		mA
Power Supply Rejection Ratio	PSRR	V _{OUT} =5V, I _{LOAD} =1mA, V _{IN} = 12V, f = 100Hz		70		dB
Thermal Shutdown Temperature	T _{SD}	I _{LOAD} =10mA	--	160	--	°C
Thermal Shutdown Hysteresis	ΔT _{SD}			15		°C

Note 1. Specifications are production tested at T_A=25°C. Specifications over the -40°C to 85°C operating temperature range are assured by design, characterization and correlation with Statistical Quality Controls (SQC).


Typical Operating Characteristics









Line Transient Response




Line Transient Response



Power On from EN



Power Off from EN





TECH PUBLIC

—台舟电子—


TPMIC5233-3.3YM5

36V,200mA,2uA, Higt PSRR Voltage Reaulators

www.sot23.com.tw

Package information

SOT23-5



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°