

## Size 5930 (15x7.75mm) Current Shunt Resistors

## SRC59 Series



SRC59 Series Current Shunt Resistors aid precision measurement and high-current applications. A wide range of precision shunts, designed for use with kilowatt-hour meters and other high-current applications where a high level of accuracy is required, is now available from PROSEMI.


### Features

- Power rating up to 10 W at 100°C
- Excellent long term stability
- Extremely low resistance values (down to 0.2mΩ)
- Halogen free, lead free and RoHS compliant



### Applications

- Power modules
- Frequency converters
- Current sensor for power hybrid sources
- High current for automotive
- Lithium battery protection board



Part Number	Power Rating $P_{100^{\circ}\text{C}}$ (W)	Resistance Range (mΩ)	TCR (ppm/°C)	Thickness (mm)	Material
SRC59F_A2R0	6	2	±50	0.94±0.1	FeCrAl
SRC59F_A1R0	6	1	±50	1.37±0.1	FeCrAl
SRC59M_AOR50	6	0.5	±75	1.09±0.1	MnCu
SRC59M_SOR30	7	0.3	±100	1.45±0.1	MnCu
SRC59M_TOR20	10	0.2	±100	1.93±0.1	MnCu


- Applicable temperature range of -55°C to +170°C
- Power rating is guaranteed for use on an aluminum substrate (MCPCB) Part
- Number definition “\_” of Resistance Tolerance

## Size 5930 (15x7.75mm)

### Current Shunt Resistors

### SRC59 Series

#### Dimension



Type	L	W	T	A	p
SRC59F_A2R0	15±0.2	7.75±0.1	0.94±0.1	4.2±0.1	1.0±0.1
SRC59F_A1R0	15±0.2	7.75±0.1	1.37±0.1	4.2±0.1	1.0±0.1
SRC59M_A0R50	15±0.2	7.75±0.1	1.09±0.1	4.2±0.1	1.0±0.1
SRC59M_S0R30	15±0.2	7.75±0.1	1.45±0.1	4.2±0.1	1.0±0.1
SRC59M_T0R20	15±0.2	7.75±0.1	1.93±0.1	4.2±0.1	1.0±0.1


#### Packaging

- Quantity: 2,000pcs
- 24mm wide tape on 330mm(13 inch) diameter reel -specification EIA Standard 481.

#### Storage Conditions

- Temperature: 22~28°C, Humidity: 40~75%

#### Derating Curve




## Size 5930 (15x7.75mm)

## Current Shunt Resistors

## SRC59 Series

### Soldering Parameters



**Wave Soldering:** 260°C, 10 seconds max.  
**Infrared Reflow:** 260°C, 30 seconds max.

### IR Reflow Profile

<b>Preheat Heat</b>	
Temperature min (T <sub>min</sub> )	150°C
Temperature max (T <sub>max</sub> )	200°C
Time (T <sub>min</sub> to T <sub>max</sub> ) (t <sub>s</sub> )	60 - 120 seconds
<b>Average ramp-up rate (T<sub>max</sub> to T<sub>p</sub>)</b>	3°C/second max.
<b>Liquidous temperature (T<sub>L</sub>)</b>	217°C
Time at liquidous (t <sub>L</sub> )	60 - 150 seconds
<b>Peak temperature (T<sub>p</sub>)</b>	260+0/-5°C
<b>Time within 5°C of actual peak Temperature (t<sub>p</sub>)</b>	10 - 30 seconds
<b>Average ramp-down rate (T<sub>p</sub> to T<sub>max</sub>)</b>	6°C/second max.
<b>Time 25 °C to peak temperature</b>	8 minutes max.

### Performances

<b>Short Time Overload</b>	Loading 5 times rate power 5sec
<b>Moisture Resistance</b>	The specimens shall be placed in a chamber and subjected to a relative humidity of 90~98% percent and a temperature of 25°C / 65°C 10 cycles
<b>High Temperature Exposure</b>	The chip (mounted on board) is exposed in the heat chamber 125°C for 1000 hrs.
<b>Rapid Change of Temperature</b>	The chip (mounted on board) is exposed, -55±3°C (30min.)/+125±2°C (30min.) for 5 cycles.
<b>Load Life</b>	Apply rated power for 1000 hours with 1.5 hours ON and 0.5 hour OFF.

© 2017 PROSEMI Inc. All Rights Reserved.  
 Specifications and features are subject to change without notice.  
[www.prosemitech.com](http://www.prosemitech.com)

The PROSEMI logo, and all other PROSEMI trademarks are the property of PROSEMI Inc. All other trademarks are the property of their respective owners.