

# V: 2020.02 SIM68D SIMCom GNSS Module



# **Product Description**

SIM68D is a high performance and reliable GNSS module. It is a standalone L1 +L5 dual-band GNSS module in a LCC type with AIROHA's high sensitivity navigation engine, which allows customer to achieve industry's high level sensitivity, accuracy, and Time-to-First-Fix (TTFF) with lower power consumption.

SIM68D provides simultaneous GPS, GLONASS, BeiDou , Galileo and QZSS open service L1 reception capability and GPS, BeiDou, Galileo and QZSS open service L5 reception capability. SIM68D can acquire and track any mix of multiple satellite signals. Combining advanced AGPS called EASY™ (Embedded Assist System) with proven AlwaysLocate™ technology, SIM68D achieves the highest performance and fully meets the industrial standard.

# **Key Benefits**

LNA

- L1 and L5 dual-band GNSS receiver
- Support EASY<sup>™</sup> self-generated orbit prediction

UART

- Support EPO™ orbit prediction
- Support SBAS ranging (WAAS, EGNOS, GAGAN, MSAS)
- Support Jamming Removing
- Low-noise amplifier has been integrated

Copyright © 2020 SIMCom Wireless Solutions Limited All Rights Reserved Building B, SIM Technology Building, No.633, Jinzhong Road Changning District, Shanghai P.R.China Tel: 86-21-31575100 Email: support@simcom.com Web: www.simcom.com

PPS



#### **Mechanical data**

Dimensions	16*12.2*2.4mm
Weight	1g

#### **Features**

Support L1: BeiDou/GPS/GLONASS/Galileo/QZSS L5: BeiDou/GPS/Galileo/QZSS
Support EASY™ self-generated orbit prediction
Support EPO™ orbit prediction
Support SBAS ranging (WAAS, EGNOS, GAGAN, MSAS)
Support Jamming Removing
Low-noise amplifier has been integrated
Support DGPS (RTCM)
Indoor and outdoor multi-path detection and compensation
LOCUSTM logger function

#### **Performance data**

Receiver type	L1: 75SVs L5: 60SVs
Max. update rate	10Hz
Sensitivity <sup>1</sup>	
Tracking	-166dBm
Reacquisition	-160dBm
Cold starts	-148dBm
Time-To-First Fix <sup>2</sup>	
Cold starts	27s
Warm start	25s
Hot starts	<1s
EPO Assist	13s
Accuracy	
Automatic Position <sup>3</sup>	1.5M
Speed <sup>4</sup>	TBD
Operation temperature <sup>5</sup>	-40°C∼+85 °C

#### Interfaces

Serial interfaces	UART
	SPI
	I2C
Digital I/O	Pulse-per-second (PPS)
	EINT0 input
Protocols	NEMA
	РМТК

### **Certifications**

TBD

#### Note

- 1. Demonstrated in lab
- 2. All SV @ -130 dBm
- 3. 50% 24 hr static, -130dBm
- 4.50%@ 30m/s
- 5. When at  $-40^{\circ}$ C~  $-30^{\circ}$ C, the sensitivity will be somewhat worse
- 6. @3.3V with a passive antenna

Copyright © 2020 SIMCom Wireless Solutions Limited All Rights Reserved Building B, SIM Technology Building, No.633, Jinzhong Road Changning District, Shanghai P.R.China Tel: 86-21-31575100 Email: support@simcom.com Web: www.simcom.com

#### **Electrical data**

Power supply	2.8V~4.3V
Backup power	2.3V~4.6V
Power consumption <sup>2</sup>	2,6:
Acquisition	23.3mA
Tracking	23.9mA
Sleep current	340uA
Backup	78uA
Antenna type	Active and passive
Antenna power	External or internal VCC_RF