



■ Specifications:

- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding voltage:1000V AC/minute
- Temperature range:-25 °C~+85°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ
- After environmental testing:≤20mΩ
- Male contact Retention force:≥20N

X2509 W V - XXS -N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① XKB Series No.
- ② Category:W-WAFER
- ③ Welding Board Angle:R-90°
- ④ Row No.-pin No.:2*XX-04P~20P
- ⑤ S:With positioning column
- ⑥ Material:NO-PA66 94V-0
- ⑦ Plating Category :SN-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.50	5.70	11	25.00	30.00	28.20
03	5.00	10.00	8.20	12	27.50	32.50	30.70
04	7.50	12.50	10.70	13	30.00	35.00	33.20
05	10.00	15.00	13.20	14	32.50	37.50	35.70
06	12.50	17.50	15.70	15	35.00	40.00	38.20
07	15.00	20.00	18.20				
08	17.50	22.50	20.70				
09	20.00	25.00	23.20				
10	22.50	27.50	25.70				

X2509WV-XXS-N0SN	PA66 UL 94V-0	X2509T	X2509H
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

Δx	日期
生Δx	日期
效Δx	日期
MARK	日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
			XKB	ANGLAR ±5°
				L≤4 ±0.2
				4<L≤16 ±0.3
				16<L≤63 ±0.4
				L>63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X2509WV-XXS-N0SN
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET 1/1
			REVISION A0