

MPS SERIES

◆ FEATURES

- Low dissipation factor, small and high current.
- For applications where high frequency, high current are required. (TV, display monitor, power supply, lighting inverter, etc)
- Coated with flame-retardant (UL94 V-0) epoxy resin.
- RoHS compliance.




◆ SPECIFICATIONS

Category temperature	-40 ~ +105°C
Rated voltage (U <sub>R</sub> )	250VDC, 450VDC, 630VDC
Capacitance tolerance	±3%(H), ±5%(J), ±10%(K)
tanδ	0.001max at 1kHz
Voltage proof	U <sub>R</sub> ×150% 60s
Insulation resistance	0.33μF ≤ :25000MΩmin 0.33μF < :7500ΩFmin
Reference standard	JIS C 5101-16, JIS C 5101-1

◆ OUTLINE

(mm)



◆ PART NUMBER



◆ PERMISSIBLE CURRENT FOR FREQUENCY

