


Voltage rating:500V AC/DC

额定电压: 500V AC/DC

Current rating:2.4A

额定电流: 2.4A

Insulation resistance:1000MΩ Min



绝缘电阻: 1000MΩ Min

Withstanding voltage:≥500V AC/minute

耐压: ≥500VC/分钟



Temperature range:-40℃-+105℃

使用温度: -40℃-+105℃




X9127 W V -XX - 9T SW X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:W-wafer
- ③ Welding Board Angle:V- Straight 180°
- ④ Row No.-Pin No.:XX-04P~26P
- ⑤ Material:9T-Nylon 9T UL94V-0
- ⑥ Planting Category:SW-Bright Tin plating
- ⑦ Color: BK-Black W-White



CCT SIZE	BIM.A	BIM.B	BIM.C	BIM.D	CCT SIZE	BIM.A	BIM.B	BIM.C	BIM.D
4	8.86	6.35	3.81	7.66	16	24.10	21.59	19.05	22.90
6	11.40	8.89	6.35	10.20	18	26.64	24.13	21.59	25.44
8	13.94	11.43	8.89	12.74	20	29.18	26.67	24.13	27.98
10	16.48	13.94	11.43	15.28	22	31.72	29.21	26.67	30.52
12	19.02	16.51	13.97	17.82	24	34.26	31.75	29.21	33.06
14	21.56	19.05	16.51	20.36	26	36.80	34.29	31.75	35.60

X9127WV-XX-9TSWBK	Black	Nylon 9T UL94V-0	Brass	Tin-Plated
X9127WV-XX-9TSWW	White			
PART NO	Color	Material	Material(Pin)	Finish(Pin)

								DSND		SCALE: N/A	MODEL TYPE: 1.27mm Crimp Style Connectors		
Δx					ANGLAR	$\pm 5^{\circ}$		DWN		VIEW: 	PART NO.: X9127WV-XX-9TSWX		
Δx					$4 < L \leq 16$	± 0.3		CHKD		UNIT: mm/in	DWG NO.: X-X9127WV-XX-9TSWX		
Δx					$16 < L \leq 63$	± 0.4		APPD		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED							
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn									WEIGHT SHEET REVISION				
									1/1 A0				