


# LESD8H5.0CT5G Transient Voltage Suppressors

## Features

- Low clamping voltage
- Complies with IEC 61000-4-2 standards:
  - Air discharge:  $\pm 20\text{kV}$
  - Contact discharge:  $\pm 20\text{kV}$
- RoHS Compliant

**LESD8H5.0CT5G**

## Ordering information

Device	Package	Shipping
LESD8H5.0CT5G	SOD882	10000/Tape&Reel

## Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	300	W
Peak Pulse Current (8/20μs)	I <sub>PP</sub>	20	A
Operating Temperature Range	T <sub>J</sub>	-55 to +125	°C
Storage Temperature Range	T <sub>stg</sub>	-55 to +150	°C

# LESD8H5.0CT5G

## ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

Symbol	Parameter
$I_{PP}$	Maximum Reverse Peak Pulse Current
$V_C$	Clamping Voltage @ $I_{PP}$
$V_{RWM}$	Working Peak Reverse Voltage
$I_R$	Maximum Reverse Leakage Current @ $V_{RWM}$
$V_{BR}$	Breakdown Voltage @ $I_T$
$I_T$	Test Current
$P_{pk}$	Peak Power Dissipation
C	Capacitance @ $V_R = 0$ and $f = 1.0$ MHz



## ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

Device	Device Marking	$V_{BR}$ (V) @ $I_T = 1\text{mA}$ (Note 1)				C (pF)	$V_C$ (V) @ $I_{PP} = 1\text{A}$ $t_p=8/20\mu\text{s}$ (Note 2)	$I_{PP}$ (A) $t_p=8/20\mu\text{s}$	$P_{pp}$ (W)	$V_C$
		$V_{RWM}$ (V)	$I_R$ (nA) @ $V_{RWM}$	Max	Min	Max	Typ	Max	Max	Max
LESD8H5.0CT5G	A9	5.0	100	6	9	80	9.5	20	300	Figures 1 and 2 See Below

1.  $V_{BR}$  is measured with a pulse test current  $I_T$  at an ambient temperature of  $25^\circ\text{C}$ .
2. Surge current waveform per Figure 5.
3. For test procedure see Figures 3 and 4.




Figure 1. ESD Clamping Voltage Screenshot  
Positive 8 kV Contact per IEC61000-4-2




Figure 2. ESD Clamping Voltage Screenshot  
Negative 8 kV Contact per IEC61000-4-2

**IEC 61000-4-2 Spec.**

Level	Test Voltage (kV)	First Peak Current (A)	Current at 30 ns (A)	Current at 60 ns (A)
1	2	7.5	4	2
2	4	15	8	4
3	6	22.5	12	6
4	8	30	16	8




Figure 3. IEC61000-4-2 Spec




Figure 4. Diagram of ESD Test Setup






Figure 5. 8 X 20  $\mu$ s Pulse Waveform


**LESD8H5.0CT5G**
**OUTLINE AND DIMENSIONS**
**SOD882**


TOP VIEW




BOTTOM VIEW

SOD882			
Dim	Min	Typ	Max
D	0.95	1.00	1.05
E	0.55	0.60	0.65
e	-	0.64	-
L	0.44	0.49	0.54
b	0.20	0.25	0.30
A	0.43	0.48	0.53
A1	0	-	0.05
A3	0.127REF.		
All Dimensions in mm			



SIDE VIEW

**SOLDERING FOOTPRINT**
**SOD882**


Dimensions	(mm)
c	0.70
G	0.30
X	0.40
X1	1.10
Y	0.70