

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 19

ALL RIGHTS RESERVED.

LOC
DSDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	REVISED ((ECR-17-016272))	19.FEB.'18	KT	YJ

3D VIEW
SCALE 2:1

NOTES;

1 MATERIAL: CuNiSi ALLOY
 2 FINISH: PRE-TIN PLATED
 3. GENERAL TOLERANCE: ± 0.2 , $\pm 3^\circ$
 4. THIS PRODUCT IS DESIGNED TO BE COMPATIBLE WITH UN-SEALED APPLICATIONS.
 5. APPLICATOR FEED: 10.0
 6. MATING TAB THICKNESS: 0.63 ± 0.03
 7 THREE SERRATIONS CENTERED IN WIRE BARREL
 8 SEVEN SERRATIONS CENTERED IN WIRE BARREL
 9 COMBINED BARREL AND SEVEN SERRATIONS

SECTION B-B

SECTION C-C

PRELIMINARY - NOT RELEASED YET

SECTION A-A

SECTION B-B

SECTION C-C

7	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	1.4 - 1.9	0.5 - 0.75SQ	2	1	060 REC GOLD (S)	1-2109006-2
7	(2.45)	2.4	Ø1.3	(1.7)	1.7	Ø0.8	1.0 - 1.5	0.22 - 0.35SQ	2	1	060 REC GOLD (SS)	1-2109006-1
8	(3.75)	3.65	Ø2.0	(2.95)	2.6	Ø1.3	Ø1.8	AL 1.25SQ	2	1	AL 060 REC (M)	8-2109006-3
8	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	Ø1.4	AL 0.75SQ	2	1	AL 060 RECEPT (S)	8-2109006-2
9	(2.65)	2.52	Ø1.4	(2.35)	2.12	Ø1.1	Ø1.4	AL 0.75SQ	2	1	AL 060 RECEPT	9-2109006-2
7	(3.75)	3.65	Ø2.0	(2.95)	2.6	Ø1.3	1.8 - 2.4	0.85 - 1.25SQ	2	1	060 RECEPT (M)	2109006-3
7	(2.9)	2.8	Ø1.7	(2.3)	2.2	Ø1.1	1.4 - 1.9	0.5 - 0.75SQ	2	1	060 RECEPT (S)	2109006-2
7	(2.45)	2.4	Ø1.3	(1.7)	1.7	Ø0.8	1.0 - 1.5	0.22 - 0.35SQ	2	1	060 RECEPT (SS)	2109006-1
SHAPE	(F)	E	ØD	(C)	B	ØA	INSUL RANGE	WIRE RANGE	FINISH	MATERIAL	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
KT JUNGCHK
KT LIMAPVD
HG CHO

PRODUCT SPEC

108-61116

APPLICATION SPEC

114-61036

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

.060 RECEPT. CONTACTS

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-2109006 -

SCALE 5:1 SHEET 1 OF 1 REV A4

MISSING DIMENSIONS ARE SAME WITH THREE SERRATIONS

1470-19 (3/11)