



## GENERAL DESCRIPTION

SE87XX series is designed for power-sensitive applications. It includes a precision and high voltage input stage, an ultra-low-power bias current branch, and results in a ultra-low-power and low-dropout linear regulator.

The SE87XX operates from an input voltage of  $V_{OUT}+1V$  to 40V, consumes only  $2.6\mu A$  of quiescent current, and offers 1% initial accuracy and SoftStart function. At power startup, the output voltage overshoot is less than 100mV.

The SE87XX regulators is available in standard SOT89-3L, and SOT23-3L packages. Standard products are Pb-free and Halogen-free.


## FEATURES

- Input voltage: 4.5V~40V
- Output voltage: 1.8V~5.7V
- Output accuracy:  $<\pm 1\%$
- Output current: 100mA (Typ.)
- PSRR: 60dB @ 100Hz
- Quiescent current:  $4.2\mu A$  @  $VIN = 12V$ (Typ.)
- ESD HBM: 3KV
- Recommend capacitor:  $10\mu F$
- No overshoot from short circuit recovery
- UVLO at 1.8V

## APPLICATIONS

- Battery-powered Smoke sensor
- Smoke sensor
- Microcontrollers
- Household appliances and instruments

## TYPICAL APPLICATION CIRCUIT







In plugging in application,  $C_{IN}$  is recommended to use  $10\mu F$  electrolytic capacitor or  $10\mu F$  MLCC with 2 ohm serial resistors to prevent large input voltage spike when plugging in. See APPLICATION INFORMATION for more information.



## PIN CONFIGURATION


(Customer pin assignments are available)



## PIN DESCRIPTION

SYMBOL	I/O	DESCRIPTION
GND	Ground	Ground
VIN	Power	Input
VOUT	O	Output

## ORDERING INFORMATION




**ABSOLUTE MAXIMUM RATINGS** (Note)

SYMBOL	ITEMS	VALUE	UNIT
V <sub>IN</sub>	Input Voltage	-0.3~45	V
V <sub>OUT</sub>	Output Voltage	-0.3~6.5	V
P <sub>DMAX</sub>	Power Dissipation	OTP limited	W
T <sub>J</sub>	Junction Temperature	-40~150	°C
T <sub>STG</sub>	Storage Temperature	-55 to 150	°C
T <sub>SOLDER</sub>	Package Lead Soldering Temperature (10s)	260	°C
ESD MM	Machine Mode	200	V
ESD HBM	Human Body Mode	3000	V
θ <sub>JA</sub>	Thermal Resistance, Junction-to-Ambient	165 (SOT89)	°C/W
		280 (SOT23)	
P <sub>D</sub>	Power Consumption	750 (SOT89)	mW
		250 (SOT23)	

*Note:* Exceed these limits to damage to the device. Exposure to absolute maximum rating conditions may affect device reliability.

**RECOMMENDED OPERATING RANGE**

SYMBOL	ITEMS	VALUE	UNIT
V <sub>IN</sub>	V <sub>IN</sub> Supply Voltage	4.5 to 40	V
R <sub>θJA</sub>	Thermal Resistance on PCB	45	°C/W
T <sub>OPT</sub>	Operating Temperature	-40 to +105	°C

**SIMPLIFIED BLOCK DIAGRAM**



## ELECTRICAL CHARACTERISTICS


( $V_{IN}=12V$  ;  $T_j=25^{\circ}C$  unless otherwise noted.)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$V_{IN}$	Input Supply Voltage		4.5		40	V
$V_{OUT}$	Output Voltage Accuracy	$I_{OUT}=10mA$	-1%		1%	V
			-2%		2%	V
				4.5	8	$\mu A$
$I_Q$	Quiescent Current			150	200	mA
$V_{DROP}$	Dropout Voltage	$I_{OUT}=10mA$		60		mV
		$\Delta V_{OUT} = -V_{OUT} * 2\%$		600		mV
		$I_{OUT}=100mA$				
		$\Delta V_{OUT} = -V_{OUT} * 2\%$				
$V_{LR}$	Load Regulation	$1mA \leq I_{OUT} \leq 100mA$		20		mV
$V_{SR}$	Line Regulation	$I_{OUT}=1mA$ , $V_{IN}=(V_{OUT}+4V)$ to 45V		0.08		%/V
PSRR	Power Supply Rejection Ratio ( $V_{in}=10V$ , $V_{PP}=0.5V$ , $I_{out}=1mA$ )	Freq=100Hz		60		dB
		Freq=1KHz		50		dB
		Freq=10KHz		40		dB
$I_{LIMIT}$	Current Limit	$V_{IN}=(V_{OUT}+1V)$ to 30V $R_{LOAD}=V_{OUT}/1A$		350		mA
$T_{SHDN}$	Thermal Protection			165		$^{\circ}C$
$TC_{VOUT}$	Output Voltage Temperature Coefficient	$I_{OUT}=10mA$ $-40^{\circ}C \leq T_{AMB} \leq 100^{\circ}C$		$\pm 100$		ppm/ $^{\circ}C$


## TYPICAL PERFORMANCE CHARACTERISTICS







$C_{IN} = 10\mu F$ ,  $C_{OUT} = 10\mu F$ ,  $T_{OPT} = 25^{\circ}C$ , unless specified otherwise. (SE87XXK2B Package)


IQ vs. Input Voltage




IQ vs. Input Voltage






IQ vs. I<sub>OUT</sub>

## Power ON/OFF

CH1 : V<sub>IN</sub>CH2 : V<sub>OUT</sub>V<sub>IN</sub>=40VI<sub>OUT</sub>=1mAV<sub>OUT</sub>=5V

## Line Transient

CH1: V<sub>IN</sub>CH2 : V<sub>OUT</sub>V<sub>IN</sub>=6V-12VI<sub>OUT</sub>=1mAV<sub>OUT</sub>=5VV<sub>IN</sub>=6V-12VI<sub>OUT</sub>=10mAV<sub>OUT</sub>=5V



## APPLICATION INFORMATION

### INPUT CAPACITOR

An input capacitor of  $10\mu F$  is required between the VIN and GND pin. The capacitor shall be placed as close as possible to VIN pin, and the use of electrolytic capacitors is recommended.

### OUTPUT CAPACITOR


The recommended is  $10\mu F$  MLCC capacitor. The minimum capacitance for stable and correct operation is  $1\mu F$ .

### NO-LOAD STABILITY

The SE87XX will remain stable and in regulation with no external load. This is especially important in CMOS RAM keep-alive applications.

### TYPICAL CIRCUIT

The following figure shows a typical application circuit for the SE87XX devices. Please keep in mind that in-rush current can push up the Vin overshoot by as much as 50%. For example, when  $Vin=30V$ , the in-rush caused spike voltage can be as high as  $45V$ . Therefore the voltage rating of  $C_{in}$  needs to be higher than 50% of the application.




In live insertion application, it is suggested that R, C1 are selected as following:

- 1.C1= $10\mu F \sim 100\mu F$  electrolytic capacitor with maximum voltage greater than  $50V$ ,  $R=0$
- 2.If the average current is known, for example at  $10mA$ , then for an input voltage of  $20V$ , the  $C1=1\mu F \sim 10\mu F$  ceramic or electrolytic with maximum voltage greater than  $40V$  and  $R=1K\Omega$  in the type of 1206 at  $1/4W$  rating can be selected.

**PACKAGE OUTLINE**

Package	SOT89-3L	Devices per reel	1000Pcs	Unit	mm
Package Dimension:					
Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
A	1.400	1.600	0.055	0.063	
b	0.320	0.520	0.013	0.020	
b1	0.400	0.580	0.016	0.023	
c	0.350	0.440	0.014	0.017	
D	4.400	4.600	0.173	0.181	
D1	1.45	1.65	0.057	0.065	
E	2.300	2.600	0.091	0.102	
E1	3.940	4.250	0.155	0.167	
e	1.500 TYP		0.060 TYP		
e1	3.000 TYP		0.118 TYP		
L	0.900	1.200	0.035	0.047	

**PACKAGE OUTLINE**

Package	SOT23-3L	Devices per reel	3000Pcs	Unit	mm																																																																								
Package Dimension:																																																																													
																																																																													
<table border="1"><thead><tr><th rowspan="2">Symbol</th><th colspan="2">Dimensions In Millimeters</th><th colspan="2">Dimensions In Inches</th></tr><tr><th>Min</th><th>Max</th><th>Min</th><th>Max</th></tr></thead><tbody><tr><td>A</td><td>1.050</td><td>1.250</td><td>0.041</td><td>0.049</td></tr><tr><td>A1</td><td>0.000</td><td>0.100</td><td>0.000</td><td>0.004</td></tr><tr><td>A2</td><td>1.050</td><td>1.150</td><td>0.041</td><td>0.045</td></tr><tr><td>b</td><td>0.300</td><td>0.500</td><td>0.012</td><td>0.020</td></tr><tr><td>c</td><td>0.100</td><td>0.200</td><td>0.004</td><td>0.008</td></tr><tr><td>D</td><td>2.820</td><td>3.020</td><td>0.111</td><td>0.119</td></tr><tr><td>E</td><td>1.500</td><td>1.700</td><td>0.059</td><td>0.067</td></tr><tr><td>E1</td><td>2.650</td><td>2.950</td><td>0.104</td><td>0.116</td></tr><tr><td>e</td><td colspan="2">0.950(BSC)</td><td colspan="2">0.037(BSC)</td><td></td></tr><tr><td>e1</td><td>1.800</td><td>2.000</td><td>0.071</td><td>0.079</td><td></td></tr><tr><td>L</td><td>0.300</td><td>0.600</td><td>0.012</td><td>0.024</td><td></td></tr><tr><td>θ</td><td>0°C</td><td>8°C</td><td>0°C</td><td>8°C</td><td></td></tr></tbody></table>					Symbol	Dimensions In Millimeters		Dimensions In Inches		Min	Max	Min	Max	A	1.050	1.250	0.041	0.049	A1	0.000	0.100	0.000	0.004	A2	1.050	1.150	0.041	0.045	b	0.300	0.500	0.012	0.020	c	0.100	0.200	0.004	0.008	D	2.820	3.020	0.111	0.119	E	1.500	1.700	0.059	0.067	E1	2.650	2.950	0.104	0.116	e	0.950(BSC)		0.037(BSC)			e1	1.800	2.000	0.071	0.079		L	0.300	0.600	0.012	0.024		θ	0°C	8°C	0°C	8°C	
Symbol	Dimensions In Millimeters		Dimensions In Inches																																																																										
	Min	Max	Min	Max																																																																									
A	1.050	1.250	0.041	0.049																																																																									
A1	0.000	0.100	0.000	0.004																																																																									
A2	1.050	1.150	0.041	0.045																																																																									
b	0.300	0.500	0.012	0.020																																																																									
c	0.100	0.200	0.004	0.008																																																																									
D	2.820	3.020	0.111	0.119																																																																									
E	1.500	1.700	0.059	0.067																																																																									
E1	2.650	2.950	0.104	0.116																																																																									
e	0.950(BSC)		0.037(BSC)																																																																										
e1	1.800	2.000	0.071	0.079																																																																									
L	0.300	0.600	0.012	0.024																																																																									
θ	0°C	8°C	0°C	8°C																																																																									

**PACKAGE OUTLINE**

Package	SOT23-5L	Devices per reel	3000Pcs	Unit	mm																																																											
Package Dimension:																																																																
<table border="1"><thead><tr><th colspan="5">DIMENSIONS</th></tr><tr><th>DIM<sup>N</sup></th><th colspan="2">INCHES</th><th colspan="2">MM</th></tr><tr><th></th><th>MIN</th><th>MAX</th><th>MIN</th><th>MAX</th></tr></thead><tbody><tr><td>A</td><td>0.110</td><td>0.120</td><td>2.80</td><td>3.05</td></tr><tr><td>B</td><td>0.059</td><td>0.070</td><td>1.50</td><td>1.75</td></tr><tr><td>C</td><td>0.036</td><td>0.051</td><td>0.90</td><td>1.30</td></tr><tr><td>D</td><td>0.014</td><td>0.020</td><td>0.35</td><td>0.50</td></tr><tr><td>E</td><td>-</td><td>0.037</td><td>-</td><td>0.95</td></tr><tr><td>F</td><td>-</td><td>0.075</td><td>-</td><td>1.90</td></tr><tr><td>H</td><td>-</td><td>0.006</td><td>-</td><td>0.15</td></tr><tr><td>J</td><td>0.0035</td><td>0.008</td><td>0.090</td><td>0.20</td></tr><tr><td>K</td><td>0.102</td><td>0.118</td><td>2.60</td><td>3.00</td></tr></tbody></table>					DIMENSIONS					DIM <sup>N</sup>	INCHES		MM			MIN	MAX	MIN	MAX	A	0.110	0.120	2.80	3.05	B	0.059	0.070	1.50	1.75	C	0.036	0.051	0.90	1.30	D	0.014	0.020	0.35	0.50	E	-	0.037	-	0.95	F	-	0.075	-	1.90	H	-	0.006	-	0.15	J	0.0035	0.008	0.090	0.20	K	0.102	0.118	2.60	3.00
DIMENSIONS																																																																
DIM <sup>N</sup>	INCHES		MM																																																													
	MIN	MAX	MIN	MAX																																																												
A	0.110	0.120	2.80	3.05																																																												
B	0.059	0.070	1.50	1.75																																																												
C	0.036	0.051	0.90	1.30																																																												
D	0.014	0.020	0.35	0.50																																																												
E	-	0.037	-	0.95																																																												
F	-	0.075	-	1.90																																																												
H	-	0.006	-	0.15																																																												
J	0.0035	0.008	0.090	0.20																																																												
K	0.102	0.118	2.60	3.00																																																												

**Customer Support**Seaward Electronics Incorporated – China

Section B, 2nd Floor, ShangDi Scientific Office Complex, #22 XinXi Road

Haidian District, Beijing 100085, China

Tel: 86-10-8289-5700/01/05

Fax: 86-10-8289-5706

Email: sales@seawardinc.com.cn

Seaward Electronics Incorporated – North America

1512 Centre Pointe Dr.

Milpitas, CA95035, USA

Tel: 1-650-444-0713