



3D VIEW

Specifications:

规格:
 Current rating:5A AC/DC
 额定电流: 5A AC/DC
 Voltage rating:500V AC
 额定电压: 500V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-25℃~+105℃
 温度范围: -55℃~+105℃
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT+30% GF UL 94V-0
 绝缘体: pbt+30% gf ul 94-0
 SHELL:STEEL, NI FINISHED
 外壳: 钢、聂加工
 CONTACT MATERIAL:BRASS SELEVITE GOLD FINISHED
 触点材料: 黄铜SELEVITE

X03 XX F X X X X

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09,15;25;37
- ③ Welding Board Angle :F-Fmale
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

| NO. OF CONTACT | A | B | C |
|----------------|-------|-------|-------|
| 09 | 30.80 | 24.99 | 16.35 |
| 15 | 39.20 | 33.30 | 24.75 |
| 25 | 53.05 | 47.04 | 38.35 |
| 37 | 69.40 | 63.50 | 54.75 |

| 铆合方式 | TYPE-1: 铆合 | TYPE-6: 直铆锁 | TYPE-3: 叉锁 | TYPE-2: 铆合锁螺丝 |
|------|------------|-------------|------------|---------------|
| 图式 | | | | |

| | | | | | |
|------|--|------|--|--------------------------------------|-------------|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: |
| DWN | | DATE | | VIEW: | PART NO.: |
| CHKD | | DATE | | UNIT: mm/in | DWG NO.: |
| APPD | | DATE | | SIZE: A4 | X03XXFXXXX |
| | | | | XKB INDUSTRIAL PRECISION CO.,LIMITED | WEIGHT |
| | | | | | 1.0g |
| | | | | | SHEET |
| | | | | | 1/1 |
| | | | | | REVISION |
| | | | | | A0 |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | units: mm |
|---|-------------|------|---------|----------|------------------------|
| ΔX | | | | | tolerance: X.X ±0.2mm |
| ΔX | | | | | X.XX ±0.1mm |
| ΔX | | | | | X.XXX ±0.05mm |
| | | | | | UNSPECIFIED TOLERANCES |
| REVISIONS | | | | | |
| www.xk-dg.cn www.helloxkb.com www.helloxkb.cn | | | | | |