

100V N-Channel SGT Power MOSFET

MOSFET

Metal Oxide Semiconductor Field Effect Transistor

HRG100N068GL Data Sheet

Rev. 2020 V2.0



100V N-Channel SGT Power MOSFET

Description

N-Channel SGT Power MOSFET designed by HR-Micro Semiconductor Company, according to the advanced Trench Technology. This devices provide an excellent gate charge and $R_{DS(on)}$, which leads to extremely communication and conduction losses. So it is very suitable for DC/DC converter, ideal for high-frequency switching and synchronous rectification.


Features

- Excellent gate charge x $R_{DS(on)}$ product(FOM)
- Very low on-resistance $R_{DS(on)}$
- Pb-free lead plating


Applications

- DC/DC Converter
- Ideal for high-frequency switching and synchronous rectification


DFN5x6_8L



Top View



Bottom View



Key Performance Parameters

Parameter	Value	Unit
$V_{DS@T_c=25^{\circ}C}$	100	V
$R_{DS(on),max@10V}$	7.2	mΩ
$Q_{g,typ}$	47	nC
$I_D@T_c=25^{\circ}C$	85	A
$I_{D,pulse}$	340	A
$E_{AS}^{1)}$	330	mJ

Device Marking and Package Information

Device	Package	Marking
HRG100N068GL	DFN5x6_8L	G100N068GL

Absolute Maximum Ratings $T_A = 25^\circ\text{C}$, unless otherwise noted			
Parameter	Symbol	Values	Unit
Drain-Source Voltage($V_{GS}=0V$)	V_{DS}	100	V
Continuous Drain Current ²⁾	I_D	$T_C = 25^\circ\text{C}$ 85	A
		$T_C = 100^\circ\text{C}$ 58	
Pulsed Drain Current ³⁾	$I_{D,pulse}$	340	A
Gate-Source Voltage	V_{GSS}	± 20	V
Single Pulse Avalanche Energy	E_{AS}	330	mJ
Power Dissipation	P_D	104	W
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55~+150	$^\circ\text{C}$

Thermal Resistance			
Parameter	Symbol	Max.	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	1.2	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient	R_{thJA}	55	$^\circ\text{C/W}$

Notes

- 1) $L=0.5\text{mH}$, $V_{DD}=50V$, Start $T_J=25^\circ\text{C}$.
- 2) Limited by maximum junction temperature.
- 3) Repetitive Rating: Pulse width limited by maximum junction temperature.

Electrical Characteristics T _J = 25°C, unless otherwise noted						
Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Characteristics						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = 250μA	100	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 100V V _{GS} = 0V, T _J = 25°C	--	--	1	μA
		V _{DS} = 100V V _{GS} = 0V, T _J = 125°C	--	--	100	
Gate-Source Leakage Current	I _{GSS}	V _{GS} = ±20V	--	--	±100	nA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	1	1.7	2.4	V
Drain-Source On-State-Resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 40A	--	6.3	7.2	mΩ
		V _{GS} = 4.5V, I _D = 40A	--	7.5	9	
Gate Resistance	R _G	f = 1.0MHz open drain	--	2.5	--	Ω
Dynamic Characteristics						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = 50V f = 1.0MHz	--	3100	--	pF
Output Capacitance	C _{oss}		--	238	--	
Reverse Transfer Capacitance	C _{rss}		--	8.9	--	
Total Gate Charge	Q _g	V _{DS} = 50V, I _D = 40A V _{GS} = 10V	--	47	--	nC
Gate-Source Charge	Q _{gs}		--	11.1	--	
Gate-Drain Charge	Q _{gd}		--	5.4	--	
Gate Plateau Voltage	V _{Plateau}		--	3.3	--	V
Turn-on Delay Time	t _{d(on)}	V _{DS} = 50V, V _{GS} = 10V I _D =40A, R _G = 6Ω	--	10	--	ns
Turn-on Rise Time	t _r		--	6	--	
Turn-off Delay Time	t _{d(off)}		--	51	--	
Turn-off Fall Time	t _f		--	9	--	
Drain-Source Body Diode Characteristics						
Body Diode Forward Voltage	V _{SD}	T _J = 25°C, I _{SD} = 40A V _{GS} = 0V	--	--	1.2	V
Continuous Diode Forward Current	I _S		--	--	85	A
Reverse Recovery Time	t _{rr}	I _F = 40A, di _F /dt = 100A/μs	--	55	--	ns
Reverse Recovery Charge	Q _{rr}		--	135	--	nC

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted




Figure 1. Maximum Safe Operating Area




Figure 2. Maximum Power Dissipation vs Case Temperature




Figure 3. Maximum Continuous Drain Current vs Case Temperature




Figure 4. Typical output Characteristics




Figure 5. Maximum Effective Thermal Impedance , Junction to Case

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted




Figure 6. Typical Transfer Characteristics




Figure 7. Typical Body Diode Transfer Characteristics




Figure 8. Drain-to-Source On Resistance vs Drain Current




Figure 9. Normalized On Resistance vs Junction Temperature




Figure 10. Normalized Threshold Voltage vs Junction Temperature




Figure 11. Normalized Breakdown Voltage vs Junction Temperature

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted




Figure 12. Capacitance Characteristics




Figure 13. Typical Gate Charge vs Gate to Source Voltage

Figure A: Gate Charge Test Circuit and Waveform




Figure B: Resistive Switching Test Circuit and Waveform






Figure C: Unclamped Inductive Switching Test Circuit and Waveform



Outlines DFN5x6_8L Package



SYMBOL	DIMENSIONAL REQMTS		
	MIN	NOM	MAX
A	0.9	1.055	1.17
b	0.33	0.415	0.51
c	0.78	---	0.97
D	4.7	5.04	5.4
D2	4.7	4.9	5.1
E	5.75	6.025	6.25
E1	5.6	5.775	6
e	1.27 BSC		
L	0.05	0.14	0.25
L1	0.35	0.485	0.71
L2	0.35	0.485	0.71
H	3.18	3.41	3.66
I	---	---	0.18

Disclaimer

HRM has made reasonable commercial efforts to ensure that the information given in this datasheet is correct. However, it must clearly be understood that such information is for guidance only and does not constitute any representation or form part of any offer or contract.

For documents and material available from this datasheet, HRM does not warrant or assume any legal liability or responsibility for the accuracy, completeness, or usefulness of any information, product, technology or process disclosed hereunder.

HRM reserves the rights to at its own discretion to make any changes or improvements to this datasheet. Unless said datasheet is incorporated into the formal contract, any customer should not rely on the information as any specification or product parameters duly committed by HRM. Customers are hereby advised to verify that the information contained herein is current and complete before the entering of any contract or acknowledgement of any purchase order. Accordingly, all products specified hereunder shall be sold subject to HRM's terms and conditions supplied at the time of order acknowledgement. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessarily performed.

HRM does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information contained herein shall be only permissible if such reproduction is without any modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. HRM is not responsible or liable for such altered documentation.

Resale of HRM's products with statements different from or beyond the parameters stated by HRM for that product or service voids all express or implied warranties for the associated HRM's product or service and is unfair and deceptive business practice. HRM is not responsible or liable for any such statements.

HRM's products are not authorized for use as critical components in life support devices or systems without the express written approval of HRM. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.