



REVISION RECORD			
REV	ECN	DESCRIPTION	DATE
△	ECN000006410	图纸更新	施文炜 2022/01/03

Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited.

未经允许禁止传输、复制、编辑该文档，以及利用其内容进行交流



Connection method:
1. For Solid wire, peel wire in right length, push down the wire.
2. For flexible wire, peeling wire in right length, pushdown the key & fix the wire, or wire turnned and fix then.

NOTES:

UL/CUL Standard

1. Conductor cross section : 26~12AWG

IEC Standard

1. Conductor cross section :

Wire range(Solid/Stranded)	0.2-2.5mm ²
Solid	0.2-4mm ²
Stranded	0.2-2.5mm ²
Stranded with ferrules	0.2-2.5mm ²
Stranded with plastic sleeve	0.2-2.5mm ²
Stranded with ferrules with plastic sleeve	0.2-2.5mm ²

2. Rated Voltage/Current :

Surge voltage category	III
Pollution degree	3
Rated surge voltage(kV)	8

Material:

Insulator	PA66	UL94 V-0
Conductor	Copper alloy	Sn plated
Spring	Stainless steel	
Ground pin	Copper alloy	Sn plated

General information:

- Dimension shall be interpreted per ASME Y14.5-2009
- Stripping length : 8-10mm
- Operating temperature: -40°C~+105°C
- RoHS Compliance
- Undimensioned Tolerances:

Pitch Range in mm	Nominal Dimension	Range in mm	Over mm	Over mm	Over mm	Over mm	Over mm
6	10	24	30	60	100	150	0.1/10
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30

HOW TO ORDER:

TP2.5-4-PE

Serieis
No. Color:
PE: Yellow Green

订货号 Order No.	TP2.5-4-PE	名称 Name	TP系列直插式弹簧 2.5mm ² 两进两出 接地端子	未注公差 Tolerance	表面 Surface
项目 Item	签字 Signature	日期 Date	图号 Drawing No.	见公差表 见公差表	VDI21
设计 Design	陈杰松	11/27/19"	/	版本号 Revision Number	重量 Weight
审核 Check	陈武	11/27/19"	材料 Material	M 0	比例 Scale
工艺 Process	-	-	见NOTES	1 of 1	1:1
标准化 Unity	-	-	物料号 Item No.		
批准 Approve	梁文龙	11/27/19"			

SUPU 宁波波普电子有限公司
NINGBO SUPU ELECTRONICS CO.,LTD.