








62P	54.84	63.50	69.32	2.41	0.58
44P	38.38	47.04	53.04	2.29	0.51
26P	24.66	33.32	39.14	2.29	0.51
15P	16.33	24.99	30.81	2.29	0.25
POS. NO.	A	B	C	D	E
DIMENSION					

P. C. BOARD LAYOUT



△			
△			
△			

SPECIFICATIONS:

Current rating:3.0A AC/DC

Voltage rating:250V AC/DC

Contact resistance:30m ohm MAX

Insulation resistance:5000M ohm MIN

Withstanding voltage:1000V AC for one minute

Operating temperature range:-40°C~+85°C

MATERIAL AND FINISH

Insulator:PBT+30%G.F(UL94V-0)

Contact:Copper Alloy Nickel Undercoated

Selective Gold Plated

Finish:Metal Iron With Tin Plated

Ordering Information

SUB		HRXX		X0XX		XX0									
Number of contacts		Housing Type		Mounting Options		Contacts Material		Contact Plated		Insulator material		Insulator color		Mark	
Code	Definition	Code	Definition	Code	Definition	Code	Definition	Code	Contact Area	Code	Definition	Code	Definition	Code	Definition
B	15 PIN	M	Male	6	SCREWED HEX SCREW ON BOARD LOCK	2	Brass	A	Gold 1u"/Light Tin	0	PBT	0	Black	0	NONE
D	26 PIN	F	Female	7	RIVETED W/ BOARD LOCK/WASHER	7	Phosphor bronze	B	Gold 3u"/Light Tin	2	NYLON	6	Blue	2	Nextron
F	44 PIN			8	RIVETED W/BOARD LOCK/ WASHER/HEX SCREW			C	Gold 5u"/Light Tin						
G	62 PIN			9	RIVETED W/ BOARD LOCK/WASHER/ ATTACHED HEX SCREW			E	Gold 15u"/Light Tin						
H	78 PIN														

nexttron

正凌精密工业股份有限公司
NEXTRON ICSENGINEERINGCORP

PART. NAME: D型XX芯高密弯式PCB焊接插座(孔)				SUB-HRBF-607A-002	
PART. NO.: SEE TABLE				DWG NAME:	
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	Tolerance
Jonnson	Jeff	allan	Jacky		
				UNITS: mm	x. ±0.50
				SCALE:	x.x ±0.30
				REVISION:	x.xx ±0.10
					xx' ±1"