


TL1014 SERIES TACT SWITCH


ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS




Audio / Visual



Computer Peripherals




Consumer Electronics



Instrumentation



Telecommunication



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 50mA @ 12VDC

Life Expectancy:

160 gf: 200,000 cycles

220 gf: 100,000 cycles

Contact Resistance: 100mΩ Max. Initial

Insulation Resistance: 100 MΩ Min. at 500V

Dielectric Strength: 250VAC for 1 min.

Operating/Storage Temperature: -40°C to 85°C

Operating Force: 160 gf, 220 gf

Travel:

160 gf: 0.25mm

220 gf: 0.30mm

Contact Arrangement: SPST

FEATURES & BENEFITS

- Tape & Reel packaging
- Multiple operating forces
- Surface mount termination
- Right angle design
- Subminiature in size

PART NUMBER CONFIGURATOR

Series	Boss	Actuation Force	Contact Plating	Termination
TL 1 0 1 4	A	F 1 6 0	Q	G
TL1014	A - No boss B - Boss	F160 - 160 gf F220 - 220 gf	Q - Silver	G - Gullwing

Specifications subject to change without notice



E-SWITCH®

www.e-switch.com




800.867.2717

2




TL1014 SERIES TACT SWITCH

BODY DIMENSIONS

A - No Boss



B - With Boss



E-SWITCH®

www.e-switch.com

800.867.2717

3

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS