


## Product Summary

- \* On-State Resistance :  $R_{DS(on)}=1.5\Omega$  @ $V_{GS}=4.5V$
- \* Driving Voltage : 2.5V
- \* Environmentally Friendly : EU RoHS Compliant, Pb Free


## Application

- \* Load/Power switch
- \* Interfacing, logic switching
- \* Battery management for ultra portable electronics

## Circuit diagram



## Package and Pin Configuration



## Absolute Maximum Ratings ( $T_A=25^\circ C$ unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNITS
Drain-Source Voltage	$V_{DSS}$	30	V
Gate-Source Voltage	$V_{GSS}$	$\pm 20$	V
Drain Current (DC)	$I_D$	0.5	A
Drain Current(Pulse) (*1)	$I_{DP}$	1	A
Channel Power Dissipation (*2)	$P_d$	0.4	W
Junction Temperature	$T_J$	150	$^\circ C$
Storage Temperature	$T_{stg}$	-55~+150	$^\circ C$

**Electrical Characteristics** ( $T_A=25^\circ\text{C}$  unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Drain-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$I_D= 250\mu\text{A}, V_{GS}= 0\text{V}$	30	-	-	V
Drain-Source Leakage Current	$I_{\text{DSS}}$	$V_{DS}= 30\text{V}, V_{GS}= 0\text{V}$	-	-	1	$\mu\text{A}$
Gate-Source Leakage Current	$I_{\text{GSS}}$	$V_{GS}= \pm 15\text{V}, V_{DS}= 0\text{V}$	-	-	$\pm 10$	$\mu\text{A}$
Gate Threshold Voltage	$V_{GS(\text{off})}$	$I_D= 250\mu\text{A}, V_{DS}= V_{GS}$	0.9	1.3	1.7	V
Drain-Source On Resistance	$R_{DS(\text{on})}$	$V_{GS}= 4.5\text{V}, I_D= 100\text{mA}$	-	0.6	1.5	$\Omega$
		$V_{GS}= 2.5\text{V}, I_D= 100\text{mA}$	-	1.5	4	$\Omega$
Input Capacitance	$C_{\text{iss}}$	$V_{DS}= 10\text{V}, V_{GS}= 0\text{V}$ $f= 1\text{MHz}$	-	40	-	pF
Output Capacitance	$C_{\text{oss}}$		-	12	-	pF
Reverse Transfer Capacitance	$C_{\text{rss}}$		-	6	-	pF
Turn-on Delay Time	$t_{d(\text{on})}$	$V_{DD}= 10\text{V}, I_D= 200\text{mA}$ $V_{GS}= 10\text{V}$	-	7	-	ns
Rise Time	$t_r$		-	5	-	ns
Turn-off Delay Time	$t_{d(\text{off})}$		-	30	-	ns
Fall Time	$t_f$		-	8	-	ns
Total Gate Charge	$Q_g$	$V_{DS}= 10\text{V}, I_D= 250\text{mA}$ $V_{GS}= 10\text{V}$	-	0.78	-	nC
Gate-Source Charge	$Q_{gs}$		-	0.1	-	nC
Gate-Drain Charge	$Q_{gd}$		-	0.16	-	nC
Diode Forward Voltage	$V_{SD}$	$I_S= 100\text{mA}, V_{GS}= 0\text{V}$	-	0.7	1.1	V


Notes:

1. Repetitive Rating: Pulse width limited by maximum junction temperature.
2. Surface Mounted on FR4 Board,  $t \leq 10$  sec.
3. Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .
4. Guaranteed by design


## Typical Electrical and Thermal Characteristic Curves

[www.sot23.com.tw](http://www.sot23.com.tw)


(1) Drain Current vs. Drain-Source Voltage




(2) Drain Current vs. Gate-Source Voltage




(3) Drain-Source On Resistance vs. Gate-Source Voltage




(4) Drain-Source On Resistance vs. Ambient Temperature




(5) Drain-Source On Resistance vs. Drain Current




(6) Source Current vs. Diode Forward Voltage




(7) Ciss, Coss, Crss vs. Drain-Source Voltage



(8) Gate-Source Voltage vs. Gate Charge




(9) Area of Safe Operation



**Package Outline Dimensions (SOT-23)**

[www.sot23.com.tw](http://www.sot23.com.tw)



Symbol	Dimensions in Millimeters	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
θ	0°	8°

**Notes**

1. All dimensions are in millimeters.
2. Tolerance  $\pm 0.10\text{mm}$  (4 mil) unless otherwise specified
3. Package body sizes exclude mold flash and gate burrs. Mold flash at the non-lead sides should be less than 5 mils.