

# 塑封高压二极管

反向电压 20KV

正向电流 5mA



# Plastic High Voltage Rectifier

Reverse Voltage 20KV

Forward Current 5mA

## 特征 Features

- $I_{F(AV)}$  5 mA
- $V_{RRM}$  20KV
- 高可靠性 High reliability

## 用途 Purpose

适用于电子设备中作高压整流用

For high voltage rectification for electronic products

## 绝对最大数值 Absolute Maximum Ratings

序号 No.	项 目 Item	符 号 Symbol	单 位 Unit	数 值 Rating	条 件 Conditions
1	Absolute Maximum Reverse Peak Reverse Voltage 反向峰值电压 Repetitive Peak Reverse Voltage	$V_{RRM}$	KV	20	
2	反向不重复峰值电压 Non-Repetitive Peak Reverse Voltage	$V_{RSM}$	KV	24	
3	正向平均电流 Average Forward Current	$I_{F(AV)}$	mA	5	50HZ 正弦半波平均值, ( $T_{amb}=50^{\circ}C$ ) 50HZ Sine-half Wave Rectification Average Value ( $T_{amb}=50^{\circ}C$ )
4	正向(不重复)浪涌电流 Non-Repetitive Forward Surge Current	$I_{FSM}$	A	0.5	50HZ 10ms 正弦半波 ( $T_{amb}=25^{\circ}C$ ) 50HZ 10ms Sine-half Wave, ( $T_{amb}=25^{\circ}C$ )
5	工作环境温度 Ambient Temperature	$T_{amb}$	°C	-40~+100	
6	最高结温 Maximum Junction Temperature	$T_{(VJ)}$	°C	120	
7	贮存温度 Storage Temperature	$T_{stg}$	°C	-40~+120	

电特性(除非另有规定,Tamb=25 °C)

Electrical Characteristics(Tamb=25°C,unless otherwise specified)

序号 NO.	项目 Item	符号 Symbol	单位 Unit	数值 Rating	测试条件 Test conditions
1	正向压降 Forward Voltage Drop	V <sub>FM</sub>	V	62.5max	I <sub>FM</sub> =10mA
2	常温反向漏电流 Normal Temperature Reverse Current	I <sub>RM1</sub>	μ A	2max	V <sub>RM</sub> =20KV
3	高温反向漏电流 High Temperature Reverse Current	I <sub>RM2</sub>	μ A	5max	Tamb=100°C V <sub>RM</sub> =20KV
4	结电容 Junction Capacitance	C <sub>j</sub>	pF	1max	1MHZ,V <sub>B</sub> =0V
5	反向恢复时间 Reverse Recovery Time	trr	μ S	0.1 max	I <sub>F</sub> =2mA,I <sub>RM</sub> =4 mA 脉冲前沿小于 0.01 μ S Fore edge of pulse less than 0.01 μ s

### 外形尺寸及标识

#### Dimensions and Marking

批号、制造商标记※

负极标记

Lot No,Corporate mark

Cathode mark

