



- Typical Specifications :
1. Rating : DC 12V 50mA
 2. Contact Resistance: 50mΩ Max
 3. Insulation Resistance: 100MΩ Min.
 4. Operation Stroke: 0.2±0.05mm
 5. Life:50,000 Cycles Min.

		NO.1			
PART NO		L1	L2	H1	H2
A: 双联上5下5	1,4	1,4	3,65	3,65	
B: 双联上5下10	1,4	6,4	3,65	8,65	
C: 双联上7下10.5	3,4	6,9	5,65	9,15	
D: 双联上10下5	6,4	1,4	8,65	3,65	
E: 双联上10下7	6,4	3,4	8,65	5,65	
F: 双联上10下10	6,4	6,4	8,65	8,65	
G: 双联上11.5下11.5	7,9	7,9	10,15	10,15	
M: 双联上11.5下17	7,9	13,4	10,15	15,65	
N: 双联上17下17	13,4	13,4	15,65	15,65	

NO.2	
PART NO	vigor
3	180±30
4	250±30

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
C	CS210/1PC

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	3	Brass(0.30t)	Plating silver	
④	Base	—	1	PPA	Black	
③	Contact	—	2	Phosphor Bronze	F.Ag	
②	Cover	—	1	SPCC	Plating Ni	
①	Keystoke	—	2	PPA	Black	

APPROVALS		DATE
DRAWN	JKUNLLU	2016/6/24

ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

ELECTRONICS CO.,LTD

 TITLE: TACT SWITCHS

 PART NO. K2-1122DQ-□□□□-□□

 SCALE: 1:1

 SHEET 1 OF 1