

**GBU**

Features

The plastic package carries Underwriters Laboratory
Flammability Classification 94V-0
Idea for printed circuit board
Glass passivated Junction chip
Low reverse leakage
High forward surge current capability
High temperature soldering guaranteed
250°C/10 seconds at terminals


Mechanical Data

Case : Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750,Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	GBU 8005G	GBU 801G	GBU 802G	GBU 804G	GBU 806G	GBU 808G	GBU 810G	UNITS
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current with heatsink	$I_{(AV)}$	8.0							A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	200.0							A
Rating for fusing ($t=8.3ms$, $T_A=25^{\circ}C$)	I_t^2	127							A^2s
Maximum instantaneous forward voltage at 8.0A	V_F	1.10							V
Maximum DC reverse current $T_A=25^{\circ}C$ at rated DC blocking voltage $T_A=125^{\circ}C$	I_R	5.0 500							μA
Typical junction capacitance (Note 1)	C_J	45.0							pF
Typical thermal resistance	R_{QA}	55.0							$^{\circ}C/W$
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +150							$^{\circ}C$

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.



Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS




FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS

