



DSR1A THRU DSR1M

Surface Mount Standard Rectifiers

Reverse Voltage - 50 to 1000 V

Forward Current - 1 A

FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Ideal for automated placement
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg 0.00048oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Top View

Marking Code : S1A-S1M

Simplified outline SOD-123FL and symbol

Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	DSR1A	DSR1B	DSR1D	DSR1G	DSR1J	DSR1K	DSR1M	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current at Ta = 65 °C	I _{F(AV)}					1			A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	I _{FSM}					30			A
Maximum Instantaneous Forward Voltage at 1 A	V _F				1.1				V
Maximum DC Reverse Current Ta = 25 °C at Rated DC Blocking Voltage Ta = 125 °C	I _R				5	50			µA
Typical Junction Capacitance ¹⁾	C _j				8				pF
Typical Thermal Resistance ²⁾	R _{θJA}				60				°C/W
Operating and Storage Temperature Range	T _j , T _{stg}				-55 ~ +150				°C

1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

2) P.C.B. mounted with 0.2x0.2"(5.0x5.0mm) copper pad areas.



DSR1A THRU DSR1M

Surface Mount Standard Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Instantaneous Reverse Characteristics




Fig.3 Typical Forward Characteristic





Fig.4 Typical Junction Capacitance






DSR1A THRU DSR1M

Surface Mount Standard Rectifiers


PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-123FL



The recommended mounting pad size



Marking

Type number	Marking code
DSR1A	S1A
DSR1B	S1B
DSR1D	S1D
DSR1G	S1G
DSR1J	S1J
DSR1K	S1K
DSR1M	S1M