

Features

- Stable breakdown voltage.
- High insulation resistance.
- Low capacitance
- Large absorbing transient current capability.
- Size: 8.0mm*8.0mm
- Storage and operating temperature: -40°C ~ +85°C
- Meets MSL level 1, per J-STD-020

Applications


- Repeaters, Modems
- Telephone Interface, Line cards
- Data communication equipment
- Line test equipment

Part Number Code

LY82R 2500 K


LY82R: Size Code, LY8 series, Two electrodes
2500: DC Breakdown Voltage=2500V@100V/s
K: Impulse Discharge Current=3KA@8/20μs

Marking



Dimensions

Item	Dimensions(mm)
D	8.0+0.3,-0.5
T	8.0+0.6,-0.1
d	0.8±0.05
L	20.0min.



Electrical Characteristics (T_A=25°C)

Model Name	DC Breakdown Voltage	Maximum Impulse Breakdown Voltage	Maximum Impulse Discharge Current	Alternating Discharge Current	Impulse Life	Minimum Insulation Resistance	Maximum Capacitance
	100V/s	1000V/μs	8/20μs, 10 times	50Hz, 1s	10/1000μs, 100A	500VDC	1MHz
LY82R2500K	2500V±20%	3600V	3KA	3A	100 times	1GΩ	1.5pF

Packaging (Bulk)

Item	PVC Tray	Inner Box	Carton
Quantity	100pcs	500pcs	5000pcs

Electrical Ratings

Items	Test Condition/Description	Requirement
DC Breakdown Voltage	The voltage is measured with a voltage rate of rise between 100V/s.	To meet the specified value
Maximum Impulse Breakdown Voltage	The maximum impulse breakdown voltage is measured with voltage ramp $dv/dt=1000V/\mu s$.	
Impulse Discharge Current	8/20 μs surge current that can be applied between two electrode, 5 positive and 5 negative surges, with 3 minutes interval time, without causing the DC breakdown voltage to change more than -20%~+30% from its initial measured value.	
Alternating Discharge Current	Rated RMS value of AC current at 50Hz, 1 sec. for 10 times with 3 minutes interval time. DC breakdown voltage shall not change more than -20%~+30% from its initial value.	
Insulation Resistance	The resistance of gas tube shall be measured between two electrodes.	
Capacitance	The capacitance of gas tube shall be measured between two electrodes. Test frequency: 1MHz	

Wave Soldering

