



# 深圳市诚芯微科技有限公司

SHENZHEN CHENGXINWEI TECHNOLOGY CO., LTD.

## N-channel Enhancement Mode Mosfet

CX4520

### DESCRIPTION


The CX4520 uses advanced trench technology to provide excellent RDS(ON) and low gate charge. This device is suitable for use as a load switch or in PWM applications.

### GENERAL FEATURES


- RDS(ON) <22mΩ @ VGS=4.5V  
RDS(ON) <15mΩ @ VGS=10V
- High Power and current handing capability
- Lead free product is acquired
- Surface Mount Package

### Application

- PWM applications
- Load switch
- Power management



Schematic diagram



Top View SOT-89

ABSOLUTE MAXIMUM RATINGS( $T_A=25^\circ\text{C}$  unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DS</sub>	45	V
Gate-Source Voltage	V <sub>GS</sub>	$\pm 20$	V
Drain Current @ Continuous (Note 2)	I <sub>D</sub> ( $25^\circ\text{C}$ )	30	A
	I <sub>D</sub> ( $100^\circ\text{C}$ )	20	A
Drain Current @ Current-Pulsed (Note 1)	I <sub>DM</sub>	112	A
Maximum Power Dissipation ( $T_A=25^\circ\text{C}$ )	P <sub>D</sub>	35	W
Operating Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55 To 150	°C

### THERMAL CHARACTERISTICS

Thermal Resistance, Junction-to-Ambient (Note 2)	R <sub>θJA</sub>	35	°C/W
--	------------------	----	------



深圳市诚芯微科技有限公司

SHENZHEN CHENGXINWEI TECHNOLOGY CO., LTD.

## N-channel Enhancement Mode Mosfet

CX4520

### ELECTRICAL CHARACTERISTICS ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	$\text{BV}_{\text{DSS}}$	$\text{V}_{\text{GS}}=0\text{V}, \text{I}_D=250\mu\text{A}$	45			V
Zero Gate Voltage Drain Current	$\text{I}_{\text{DSS}}$	$\text{V}_{\text{DS}}=24\text{V}, \text{V}_{\text{GS}}=0\text{V}$			1	$\mu\text{A}$
Gate-Body Leakage Current	$\text{I}_{\text{GSS}}$	$\text{V}_{\text{GS}}=\pm20\text{V}, \text{V}_{\text{DS}}=0\text{V}$			$\pm100$	nA
ON CHARACTERISTICS (Note 3)						
Gate Threshold Voltage	$\text{V}_{\text{GS(th)}}$	$\text{V}_{\text{DS}}=\text{V}_{\text{GS}}, \text{I}_D=250\mu\text{A}$	1		2	V
Drain-Source On-State Resistance	$\text{R}_{\text{DS(ON)}}$	$\text{V}_{\text{GS}}=4.5\text{V}, \text{I}_D=15\text{A}$		16	22	$\text{m}\Omega$
		$\text{V}_{\text{GS}}=10\text{V}, \text{I}_D=15\text{A}$		12	15	$\text{m}\Omega$
DYNAMIC CHARACTERISTICS (Note 4)						
Input Capacitance	$\text{C}_{\text{iss}}$	$\text{V}_{\text{DS}}=15\text{V}, \text{V}_{\text{GS}}=0\text{V}, \text{F}=1.0\text{MHz}$		930	1350	PF
Output Capacitance	$\text{C}_{\text{oss}}$			135	190	PF
Reverse Transfer Capacitance	$\text{C}_{\text{rss}}$			110	160	PF
SWITCHING CHARACTERISTICS (Note 4)						
Turn-on Delay Time	$\text{t}_{\text{d(on)}}$	$\text{V}_{\text{DS}}=15\text{V}, \text{V}_{\text{GS}}=10\text{V}, \text{R}_{\text{GEN}}=3.3\Omega$ $\text{I}_{\text{ds}}=15\text{A}$		4.5		ns
Turn-on Rise Time	$\text{t}_r$			9		ns
Turn-Off Delay Time	$\text{t}_{\text{d(off)}}$			32		ns
Turn-Off Fall Time	$\text{t}_f$			5		ns
Total Gate Charge	$\text{Q}_g$	$\text{V}_{\text{DS}}=15\text{V}, \text{I}_D=15\text{A}, \text{V}_{\text{GS}}=4.5\text{V}$		15		nC
Gate-Source Charge	$\text{Q}_{\text{gs}}$			4.5		nC
Gate-Drain Charge	$\text{Q}_{\text{gd}}$			7		nC
Body Diode Reverse Recovery Time	$\text{T}_{\text{rr}}$			20		ns
Body Diode Reverse Recovery Charge	$\text{Q}_{\text{rr}}$	$\text{I}_F=5\text{A}, \text{dI}/\text{dt}=100\text{A}/\mu\text{s}$		10		nC
DRAIN-SOURCE DIODE CHARACTERISTICS						
Diode Forward Voltage (Note 3)	$\text{V}_{\text{SD}}$	$\text{V}_{\text{GS}}=0\text{V}, \text{I}_S=1\text{A}$		0.80	1.2	V

#### NOTES:

1. Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$ .
2.  $\text{R}_{\theta JA}$  is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.  $\text{R}_{\theta JC}$  is guaranteed by design while  $\text{R}_{\theta CA}$  is determined by the user's board design.  $\text{R}_{\theta JA}$  shown below for single device operation on FR-4 in still air.



深圳市诚芯微科技有限公司

SHENZHEN CHENGXINWEI TECHNOLOGY CO., LTD.

## N-channel Enhancement Mode Mosfet

CX4520

### ■ Typical Performance Characteristics




Fig.1 Typical Output Characteristics




Figure 2: Transfer Characteristics (Note E)




Figure 3: On-Resistance vs. Drain Current and Gs Voltage (Note E)




Figure 4: On-Resistance vs. Junction Temperature (Note E)




Figure 5: On-Resistance vs. Gate-Source Voltage (Note E)




Figure 6: Body-Diode Characteristics (Note E)



深圳市诚芯微科技有限公司

SHENZHEN CHENGXINWEI TECHNOLOGY CO., LTD.

## N-channel Enhancement Mode Mosfet

CX4520

### ■ Typical Performance Characteristics




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note F)




Figure 10: Single Pulse Power Rating (Note F)




Figure 11: Normalized Maximum Transient Thermal Impedance (Note F)



## N-channel Enhancement Mode Mosfet

CX4520

### ■ Typical Performance Characteristics




Figure 12: Single Pulse Avalanche capability (Note C)




Figure 13: Power De-rating (Note F)




Figure 14: Current De-rating (Note F)




Figure 15: Single Pulse Power Rating Junction-to-Ambient (Note H)




Figure 16: Normalized Maximum Transient Thermal Impedance (Note H)



深圳市诚芯微科技有限公司


SHENZHEN CHENGXINWEI TECHNOLOGY CO., LTD.

N-channel Enhancement Mode Mosfet

CX4520

### Package Information

SOT89-3 Package



尺寸 标注	最小(mm)	最大(mm)	尺寸 标注	最小(mm)	最大(mm)
A	4.40	4.60	B3	0.82	0.83
A1	1.65	1.75	C	1.40	1.60
A2	2.95	3.05	C1	0.35	0.45
A3	0.35	0.45	theta	6° TYP4	
A4	0.43	0.53	theta 1	3° TYP4	
A5	0.35	0.45	theta 2	6° TYP4	
B	2.40	2.60	theta 3	3° TYP4	
B1	4.05	4.25			
B2	0.82	0.83			