Features

- Efficiency up to 91%, no need for heatsinks
- Pin-out compatible with LM78XX linears
- Low profile (LxWxH=11.6 x 8.5 x 10.4mm)

Switching Regulator

Short circuit protection

Wide input range (7V - 28V)

• IEC/EN60950-1 + AM2 certified

Description

The R-78E series is a switching regulator module that has been designed to offer all the advantages of a switching regulator (high efficiency, wide input range, accurate output voltage regulation) but with a low cost for production quantities. Due to the R-78E's high efficiency of up to 91% at an output voltage of 5V/1A at the output, no heat sink is required. The compact TO- 220 compatible SIP3 package measures only $11.6 \times 8.5 \times 10.4$ mm, so it saves precious board space. The warranty is 3 years.

Selection Guide						
Part	Input	Output	Output	Efficie	ncy ⁽¹⁾	max. Capacitive
Number	Voltage Range [VDC]	Voltage [VDC]	Current [A]	@ min. Vin [%]	@ max. Vin [%]	Load ⁽²⁾ [µF]
R-78E3.3-1.0	7-28	3.3	1.0	91	84	220
R-78E5.0-1.0	8-28	5.0	1.0	93	85	220
R-78E12-1.0/X9	15-27	12	1.0	97	93	100

Notes:

Note1: Efficiency is tested at full load at +25°C ambient Note2: Max. Cap Load is tested by nominal input and full resistive load



RECO

R-78E-1.0

1.0 Amp

Single Output

R-78E-1.0 series

(Pk

SIP3

DC/DC Converter

Model Numbering



Notes:

Note3: R-78E12-1.0/X9 is available with epoxy potting only. For more information refer to *"Material"*

Specifications (measured at Ta= 25°C, full load, Vin= 24VDC and a	after warm-up)
---	----------------

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Тур.	Max.
Input Current	min. Vin			1000mA
Quiescent Current			1.5mA	
	3.3 & 5Vout		330kHz	
Internal Operating Frequency	12Vout		570kHz	
Minimum Load	only R-78E12-1.0/X9		2%	
Output Ripple and Noise (4)	20MHz BW			120mVp-p

Notes:

Note4: Measurements are made with a 100nF MLCC across output (low ESR)

continued on next page

RECOM DC/DC Converter

R-78E-1.0 Series

Specifications (measured at Ta= 25°C, full load, Vin= 24VDC and after warm-up)

Efficiency vs. Load



REGULATIONS				
Parameter	Condition	Value		
Output Accuracy		±3.0% typ. / ±5.0% max.		
Line Regulation	low line to high line, full load	±1.0% max.		
Load Regulation	typ Vin. and 10% to 100% load	±1.5% max.		

PROTECTIONS			
Parameter	Condition	Value	
Short Circuit Protection (SCP)		Continuous, automatic recovery	

RECOM DC/DC Converter

R-78E-1.0 Series

Specifications (measured at Ta= 25°C, full load, Vin= 24VDC and after warm-up)



SAFETY AND CERTIFICATIONS		<u></u>
Certificate Type (Safety)	Report / File Number	Standard
Information Technology Equipment, General Requirements for Safety	1603123	IEC60950-1:2005, 2nd Edition + AM 2:2013 EN60950-1:2006 + AM2:2013
EAC	RU-AT.49.09571	TP TC 004/2011
RoHS2		RoHS 2011/65/EU + AM2015/863
EMC Compliance	Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements	with external filter (see filter suggestion below)	EN55032, Class A and E
Emission requirements EMC Filter Suggestion according to EN55032	(See miler suggestion below)	



Component List Class A

MODEL	C1	C2	L1	
R-78E3.3-1.0	10µF	10µF	<u>12µH choke</u>	
R-78E5.0-1.0	100V MLCC	100V MLCC	<u>RLS-126</u>	
B-78E12-1.0/X9	10µF	10µF	5.6µH choke	
n-10E12-1.0/X9	50V MLCC	50V MLCC	<u>RLS-567</u>	

Component List Class B

MODEL	C1	C2	L1
R-78E3.3-1.0	10µF	2.2µF	68µH choke
R-78E5.0-1.0	100V MLCC	100V MLCC	<u>RLS-686</u>
R-78E12-1.0	10µF 50V MLCC	10µF 50V MLCC	100µH choke <u>RLS-105</u>

Notes:

Note5: Filter suggestions are valid for indicated part numbers only. For other part numbers, please contact RECOM tech support for advice

RECOM DC/DC Converter

R-78E-1.0 Series

Specifications (measured at Ta= 25°C, full load, Vin= 24VDC and after warm-up)





PACKAGING INFORMATION			
Parameter	Туре	Value	
Packaging Dimension (LxWxH)	tube	520.0 x 11.2 x 18.2mm	
Packaging Quantity		42pcs	
Storage Temperature Range		-55°C to +125°C	

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.