







SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:−40℃ to +105℃

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V−0)
Standard: PA6T
Max.Processing Temp: 230℃ for 30−60 seconds
(260℃ for 5 seconds)



Recommended P.C.B Layout(Top Side) (PCB BOARD TOLERANCE±0.05)



N= W/O Post

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	3.80	2.50	6.50	8.00
Alternate				

				OPERATION		DRAW	YiYuSheng	12.04.11	SCALE	FIT	深圳市华灿天禄电子有限公司	
				X.X	±0.30				UNIT	mm		
				X.XX	±0.20	CHECK			SIZE	A4		
				X.XXX	±0.10				SHEET	1/1	PART NO.	PZ200—2—N—S
A0	2012.04.11	NEW DRAWING		Angle	±3°	APPROVE			PROJ.		TITLE:	2.0PH 2xNpin H2.0MM SMT 夹持量
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL							

1 2 3 4 5 6 7 8 9