






ROHS compliant

REV.	ECN NO.	DRAWN	DATE



NOTES:

1.Specification:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30 °C to +85 °C.
- 3>.Storage Temperature: -40 °C to +85 °C.
- 4>.Mechanical Life: 1000 cycles operations.
- 5>.Resistance to Soldering: 260 ±5 °C for 3-5 Seconds.

2.PLATING:


- 1>.GOLD flash 1u" (min) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>.Non-switch Rating:100mA at 50V DC.
- 2>.Switching Rating: 25mA at 24V DC.
- 3>.Contact Resistance: Inital 50mΩ Max.
Contact Resistance: After life 100mΩ Max.
- 4>.Insulation Resistance:100MΩ Min at 500VDC.
- 5>.Dielectric Strength: 500V AC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSHP XX T S G E R



5.PACKING: 2000pcs/Reel/Box.

东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.

Drawing	dengkg	Date	2017. 03. 24	LINER	ANGLES	PRODUCT Family DSHP Series Pitch 1.27mm	
Check	zhong	Scale	4:1	>0±0.05	>0° ±0.5°	PRAT NO.	DSHP02TSGER
Approved		Unit	MM	>1±0.10	>5° ±1.0°	FILE NO.	DSHP-002-S-A
Size	A4	Rev.	A	>10±0.30		PROJECTION	