


### 3-Terminal Positive Voltage Regulator



1.OUT 2.GND 3.IN  
SOT-89 Plastic Package

#### Absolute Maximum Ratings ( $T_a = 25^\circ\text{C}$ )


Parameter	Symbol	Rating	Unit
Input Voltage	$V_I$	35	V
Power Dissipation	$P_{tot}$	800 <sup>1)</sup>	mW
Operating Temperature	$T_{opr}$	-20 to +120	°C
Storage Temperature Range	$T_{stg}$	-55 to +150	°C

<sup>1)</sup> 15 mm X 25 mm X 0.7 mm alumina ceramic board,  $T_a \leq 25^\circ\text{C}$


#### Electrical Characteristics ( $T_a = 25^\circ\text{C}$ )

(Unless otherwise specified,  $0^\circ\text{C} \leq T_J \leq 125^\circ\text{C}$ ,  $V_I = 19\text{ V}$ ,  $I_O = 40\text{ mA}$ ,  $C_L = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ )

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Output Voltage	$V_O$	$T_J = 25^\circ\text{C}$	11.5	12	12.5	V
		$14.5\text{ V} \leq V_I \leq 27\text{ V}$ , $1\text{ mA} \leq I_O \leq 40\text{ mA}$	11.4	-	12.6	V
		$V_I = 19\text{ V}$ , $1\text{ mA} \leq I_O \leq 70\text{ mA}$	11.4	-	12.6	V
Line Regulation	Regline	$14.5\text{ V} \leq V_I \leq 27\text{ V}$ , $T_J = 25^\circ\text{C}$	-	-	250	mV
		$16\text{ V} \leq V_I \leq 27\text{ V}$ , $T_J = 25^\circ\text{C}$	-	-	200	
Load Regulation	Regload	$1\text{ mA} \leq I_O \leq 100\text{ mA}$ , $T_J = 25^\circ\text{C}$	-	-	100	mV
		$1\text{ mA} \leq I_O \leq 40\text{ mA}$ , $T_J = 25^\circ\text{C}$	-	-	50	
Quiescent Current	$I_Q$	$T_J = 25^\circ\text{C}$	-	-	6	mA
Quiescent Current Change	$\Delta I_Q$	$16\text{ V} \leq V_I \leq 27\text{ V}$	-	-	1.5	mA
		$1\text{ mA} \leq I_O \leq 40\text{ mA}$	-	-	0.1	
Output Noise Voltage	$V_N$	$10\text{ Hz} \leq f \leq 100\text{ KHz}$ , $T_J = 25^\circ\text{C}$	-	80	-	µV
Ripple Rejection	RR	$f = 120\text{ Hz}$ , $15\text{ V} \leq V_I \leq 25\text{ V}$ , $T_J = 25^\circ\text{C}$	37	-	-	dB
Dropout Voltage	$V_{Drop}$	$T_J = 25^\circ\text{C}$	-	1.7	-	V



### SOT-89 PACKAGE OUTLINE



<b>Symbol</b>	<b>Dimension in Millimeters</b>	
	<b>Min</b>	<b>Max</b>
A	1.40	1.60
B	0.44	0.62
B1	0.35	0.54
C	0.35	0.44
D	4.40	4.60
D1	1.62	1.83
E	2.29	2.60
e	1.50 Typ	
H	3.94	4.25
H1	2.63	2.93
L	0.89	1.20
All Dimensions In mm		