

## N-Channel Enhancement Mode MOSFET

### Description

The HX3400B uses advanced trench technology to provide excellent  $R_{DS(ON)}$ , low gate charge and high density cell Design for ultra low on-resistance. This device is suitable for use as a load switch or in PWM applications.

### General Features

- ◆  $V_{DS} = 30V$ ,  $I_D = 5.8A$
- $R_{DS(ON)}(\text{Typ.}) = 24m\Omega$    @  $V_{GS} = 4.5V$
- $R_{DS(ON)}(\text{Typ.}) = 35m\Omega$    @  $V_{GS} = 2.5V$
- ◆ High power and current handing capability
- ◆ Lead free product is acquired
- ◆ Surface mount package

### Application


- ◆ PWM applications
- ◆ Load switch

### Package

- ◆ SOT-23-3L




### Schematic diagram



### pin assignment

SOT-23-3L  
(TOP VIEW)



### Ordering Information

Part Number	Storage Temperature	Package	Devices Per Reel
HX3400B	-55°C to +150°C	SOT-23-3L	3000

NOTE: HX3400B : B It stands for SOT-23-3L

### Absolute Maximum Ratings (TA=25°C unless otherwise noted)

parameter	symbol	limit	unit
Drain-source voltage	$V_{DS}$	30	V
Gate-source voltage	$V_{GS}$	$\pm 12$	V
Drain current-continuous <sup>a</sup> @Tj=125°C -pulse d <sup>b</sup>	$I_D$	5.8	A
	$I_{DM}$	30	A
Drain-source Diode forward current	$I_S$	2	A
Maximum power dissipation	$P_D$	1.4	W
Operating junction Temperature range	Tj	-55—150	°C

**Electrical Characteristics** (TA=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
<b>OFF Characteristics</b>						
Drain-source breakdown voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	30	-	-	V
Zero gate voltage drain current	I <sub>DSS</sub>	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V	-	-	1	μA
Gate-body leakage	I <sub>GSS</sub>	V <sub>DS</sub> =0V, V <sub>GS</sub> =±12V	-	-	±100	nA
<b>ON Characteristics</b>						
Gate threshold voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	0.45	0.62	0.85	V
Drain-source on-state resistance	R <sub>DS(ON)</sub>	V <sub>GS</sub> =4.5V, I <sub>D</sub> =5A V <sub>GS</sub> =2.5V, I <sub>D</sub> =4A	-	24	35	mΩ
Forward transconductance	g <sub>f</sub>	V <sub>GS</sub> =5V, I <sub>D</sub> =5.8A	-	33	-	
<b>Dynamic Characteristics</b>						
Input capacitance	C <sub>ISS</sub>	V <sub>DS</sub> =15V, V <sub>GS</sub> =0V f=1.0MHz	-	473	-	pF
Output capacitance	C <sub>OSS</sub>		-	57	-	
Reverse transfer capacitance	C <sub>RSS</sub>		-	43	-	
<b>Switching Characteristics</b>						
Turn-on delay time	t <sub>D(ON)</sub>	V <sub>DS</sub> =15V V <sub>GS</sub> =10V R <sub>L</sub> =2.6 ohm R <sub>GEN</sub> =3ohm	-	3	-	ns
Rise time	tr		-	2.5	-	
Turn-off delay time	t <sub>D(OFF)</sub>		-	25	-	
Fall time	tf		-	4	-	
Total gate charge	Q <sub>g</sub>	V <sub>DS</sub> =15V, I <sub>D</sub> =5A V <sub>GS</sub> =4.5V	-	5.6	-	nC
Gate-source charge	Q <sub>gs</sub>		-	1.1	-	
Gate-drain charge	Q <sub>gd</sub>		-	1.2	-	
<b>DRAIN-SOURCE DIODE CHARACTERISTICS</b>						
Diode forward voltage	V <sub>SD</sub>	V <sub>GS</sub> =0V, I <sub>s</sub> =1A	-	0.76	1.16	V


**Notes:**

- a. surface mounted on FR4 board, t≤10sec
- b. pulse test: pulse width≤300μs, duty≤2%
- c. guaranteed by design, not subject to production testing


**Thermal Characteristics**

Thermal Resistance junction-to ambient	R <sub>th JA</sub>	100	°C/W
--	--------------------	-----	------


## Typical Performance Characteristics




**Fig1 Output Characteristics**




**Fig2 Transfer Characteristics**




**Fig3 Rdson-Drain current**




**Fig4 Capacitance vs Vds**




**Fig5 Rdson-Gate Drain voltage**



**Fig6 Gate Charge**




**Fig7 Power De-rating**



**Fig8 Source-Drain Diode Forward**

## Package Information

- SOT-23-3L



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
theta	0°	8°	0°	8°