



General Description

The DY 20N60WS is a high voltage power MOSFET, fabricated using advanced super junction technology. The resulting device has extremely low on resistance, low gate charge and fast switching time, making it especially suitable for applications which require superior power density and outstanding efficiency.

The 20N60WS break down voltage is 600V and it has a high rugged avalanche characteristics. The 20N60WS is available in TO-263, ITO-220, TO-220, TO-262 packages.

Features

- Ultra Low $R_{DS(ON)} = 200m\Omega @ V_{GS} = 10V$.
- Ultra Low Gate Charge, $Q_g = 25.3nC$ typ.
- Fast switching capability
- Robust design with better EAS performance
- EMI Improved

Application

- LED Lighting Power
- TV Power
- High Power AC/DC Power Supply

Part No.	Package	Packing
DMT20N60WS-TU	TO-220	50pcs / Tube
DMF20N60WS-TU	ITO-220	50pcs / Tube
DMK20N60WS-TU	TO-262	50pcs / Tube
DMG20N60WS-TU	TO-263	50pcs / Tube
DMG20N60WS-TR	TO-263	800pcs / 13" Reel

PRODUCT SUMMARY

V_{DS} (V)	$R_{DS(on)}$ (Ω)
600	0.19@ $V_{GS} = 10V$

Symbol





Figure 1 Symbol of 20N60WS

Package Type





Absolute Maximum Ratings

Parameter	Symbol	Rating	Unit	
Drain-Source Voltage	V_{DSS}	630	V	
Gate-Source Voltage	V_{GSS}	± 30	V	
Continuous Drain Current	I_D	$T_C=25^\circ\text{C}$	14.0	A
		$T_C=125^\circ\text{C}$	7.1	
Pulsed Drain Current (Note 2)	I_{DM}	43	A	
Avalanche Energy, Single Pulse (Note 3)	E_{AS}	190	mJ	
Avalanche Energy, Repetitive (Note 2)	E_{AR}	0.2	mJ	
Avalanche Current, Repetitive (Note 2)	I_{AR}	4.0	A	
Continuous Diode Forward Current	I_S	16.0	A	
Diode Pulse Current	$I_{S,PULSE}$	43	A	
Operating Junction Temperature	T_J	150	$^\circ\text{C}$	
Storage Temperature	T_{STG}	-55 to 150	$^\circ\text{C}$	
Lead Temperature (Soldering, 10 sec)	T_{LEAD}	300	$^\circ\text{C}$	

Note:

1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.
2. Repetitive Rating: Pulse width limited by maximum junction temperature
3. $I_{AS} = 4.0\text{A}$, $V_{DD} = 60\text{V}$, $R_G = 25\Omega$, Starting $T_J = 25^\circ\text{C}$



Electrical Characteristics

$T_J = 25^\circ\text{C}$, unless otherwise specified.

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Statistic Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	600			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=600V, V_{GS}=0V$			1	μA
Gate-Body Leakage Current	Forward	$I_{GSSF}, V_{GS}=30V, V_{DS}=0V$			100	nA
	Reverse	$I_{GSSR}, V_{GS}=-30V, V_{DS}=0V$			-100	
Gate Threshold Voltage	$V_{GS(TH)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	3		5	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=9.0A$		170	190	$m\Omega$
Gate Resistance	R_G	$f=1MHz, \text{Open Drain}$		2.0		Ω
Dynamic Characteristics						
Input Capacitance	C_{ISS}	$V_{DS}=50V, V_{GS}=0V, f=1MHz$		1093		pF
Output Capacitance	C_{OSS}			86.4		
Reverse Transfer Capacitance	C_{RSS}			10		
Effective output capacitance, energy related ^{NOTE4}	$C_{O(er)}$	$V_{GS}=0V, V_{DS}=0\dots 480V$		51.2		pF
Effective output capacitance, time related ^{NOTE5}	$C_{O(tr)}$			187.3		
Turn-on Delay Time	$t_{d(on)}$	$V_{DD}=400V, I_D=7.0A, R_G=10\Omega, V_{GS}=10V$		12		ns
Rise Time	t_r			20		
Turn-off Delay Time	$t_{d(off)}$			24		
Fall Time	t_f			50		
Gate Charge Characteristics						
Gate to Source Charge	Q_{gs}	$V_{DD}=480V, I_D=7.0A, V_{GS}=0 \text{ to } 10V$		7.2		nC
Gate to Drain Charge	Q_{gd}			8.1		
Gate Charge Total	Q_g			25.3		
Gate Plateau Voltage	$V_{plateau}$			5.4		V
Reverse Diode Characteristics						
Drain-Source Diode Forward Voltage	V_{SD}	$V_{GS}=0V, I_{SD}=7.0A$		0.81	1.1	V
Reverse Recovery Time	t_{rr}	$V_R=400V, I_F=7.0A, dI_F/dt=100A/\mu s$		216.9		ns
Reverse Recovery Charge	Q_{rr}			1.7		μC
Peak Reverse Recovery Current	I_{rrm}			16.1		A

Note:

4. $C_{O(er)}$ is a fixed capacitance that gives the same stored energy as C_{OSS} while V_{DS} is rising from 0 to 480V

5. $C_{O(tr)}$ is a fixed capacitance that gives the same charging time as C_{OSS} while V_{DS} is rising from 0 to 480 V



Typical Performance Characteristics









Figure 7: Typ. Output Characteristics




$I_D = f(V_{DS}); T_j = 25^\circ\text{C}; \text{parameter: } V_{GS}$

Figure 8: Typ. Output Characteristics




$I_D = f(V_{DS}); T_j = 125^\circ\text{C}; \text{parameter: } V_{GS}$

Figure 9: Typ. Drain-Source On-State Resistance



$R_{DS(ON)} = f(I_D); T_j = 125^\circ\text{C}; \text{parameter: } V_{GS}$


Figure 10: Typ. Drain-Source On-State Resistance



$R_{DS(ON)} = f(T_j); I_D = 9.0\text{A}; V_{GS} = 10\text{V}$




Figure 11: Typ. Transfer Characteristics




$I_D = f(V_{GS}); V_{DS} = 20V$

Figure 12: Typ. Gate Charge




$V_{GS} = f(Q_{gate}), I_D = 7A \text{ pulsed}$

Figure 13: Drain-Source Breakdown Voltage



$V_{BR(DSS)} = f(T_j); I_D = 1mA$


Figure 14: Forward Characteristics of Reverse Diode



$I_F = f(V_{SD}); \text{parameter: } T_j$




Figure 15: Avalanche Energy




$E_{AS}=f(T_j); I_D=4.0A; V_{DD}=60V$

Figure 16: Typ. Capacitances



$C=f(V_{DS}); V_{GS}=0; f=1MHz$

Figure 17: C_{OSS} Stored Energy





$E_{OSS}=f(V_{DS})$





Test Circuits



1. Gate Charge Test Circuit & Waveform



2. Switch Time Test Circuit





3. Unclaimed Inductive Switching Test Circuit & Waveforms






4. Test Circuit and Waveform for Diode Characteristics






TO-220 Mechanical Drawing



TO-220AB		
Unit:mm		
DIM	MIN	MAX
A	14.80	15.80
B	9.57	10.57
C	2.54	2.94
D	5.80	6.80
E	2.95	3.95
F	12.70	13.40
G	2.34	2.74
H	0.51	1.11
I	0.97	1.57
J	3.54 ϕ	4.14 ϕ
K	4.27	4.87
L	1.07	1.47
M	2.03	2.92
N	0.30	0.64


ITO-220 Mechanical Drawing



ITO-220AB		
Unit:mm		
DIM	MIN	MAX
A	14.50	15.50
B	9.50	10.50
C	2.50	2.90
D	6.30	7.30
E	3.30	4.30
F	13.00	14.00
G	2.35	2.75
H	0.30	0.90
I	0.90	1.50
J	3.20	3.80
K	4.24	4.84
L	2.52	2.92
M	1.09	1.49
N	0.47	0.64



TO-262 Mechanical Drawing



TO-263 Mechanical Drawing

