



RECOMMENDED FPC/FPC DIM.

Electrical Characteristics:
 Current rating: 0.4A AC/DC
 Voltage rating: 50V AC/DC
 Temperature range: -25°C~+85°C
 Withstand Voltage: 200V AC/Minute
 Contact Resistance: ≤ 20mΩ
 Insulation resistance: ≥ 500MΩ
 Relative Humidity: 93%~40°C

Material Description:
 Terminal: Phosphor Bronze Tin-Leadplated
 Fitting Nail: Brass Tin-plated
 Housing: Thermoplastic(U194V-0)
 Slider: Thermoplastic(U194V-0)
 Poles: 4~60P

注
 * 尺寸
 4PIn~29PIn: 4.70mm
 30PIn~39PIn: 4.80mm
 40PIn~60PIn: 4.90mm

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:
CHECKED:	DATE:
DRAWN:	DATE:
LYP	2011-01-13

深圳市灿科盟实业有限公司
SHENZHEN CHANKEMING INDUSTRY CO., LTD

标题:
 FPC0.5-34P 立贴 带锁 正牌位

PART. NO.	C3025535
UNIT	mm
SCALE	free
FILE NO.	F-FPC0N34P-D311
REV.	B JMK0