




PCB Layout

Electrical:
Current rating: 3Amps/contact max.
Contact resistance: $\leq 20\text{m}\Omega$ /contact
Insulation resistance: $\geq 1000\text{M}\Omega$ at V=100V
Withstanding voltage: 550V AC/minute
Mechanical:
Soldering temperature: +260°C, 4s max

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE: ± 0.20 

PTN NUMBER	A (mm)	B (mm)	C (mm)
6P	15.24	5.08	12.94
8P	17.78	7.62	15.48
10P	20.32	10.16	18.02
12P	22.86	12.70	20.56
14P	25.40	15.24	23.10
16P	27.94	17.78	25.64
18P	30.48	20.32	28.18
20P	33.02	22.86	30.72
22P	35.56	25.40	33.26
24P	38.10	27.94	35.80
26P	40.64	30.48	38.34
28P	43.18	33.02	40.88
30P	45.72	35.56	43.42
32P	48.26	38.10	45.96
34P	50.80	40.64	48.50
36P	53.34	43.18	51.04
40P	58.42	48.26	56.12
44P	63.50	53.34	61.20
50P	71.12	60.96	68.82
60P	83.82	73.66	81.52
64P	88.90	78.74	86.60

[illegible]