

**N-Channel 200-V (D-S) MOSFET**

**GENERAL DESCRIPTION**

The ME2620-G is the N-Channel logic enhancement mode power field effect transistors, using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on state resistance. These devices are particularly suited for low voltage application such as cellular phone, notebook computer power management and other battery powered circuits, and low in-line power loss that are needed in a very small outline surface mount package.



**FEATURES**

- $R_{DS(ON)} \leq 756m\Omega @ V_{GS}=10V$
- Super high density cell design for extremely low  $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability

**APPLICATIONS**

- Power Management in Note book
- DC/DC Converter
- Load Switch
- LCD Display inverter

**PIN CONFIGURATION**



N-Channel MOSFET

Ordering Information: ME2620-G (Green product-Halogen free)

**Absolute Maximum Ratings (TA=25°C Unless Otherwise Noted)**

Parameter	Symbol	Maximum Ratings	Unit
Drain-Source Voltage	$V_{DS}$	200	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current	$I_D$	$T_A=25^\circ C$	1.4
		$T_A=70^\circ C$	1.1
Pulsed Drain Current	$I_{DM}$	5	A
Maximum Power Dissipation	$P_D$	$T_A=25^\circ C$	2.2
		$T_A=70^\circ C$	1.4
Operating Junction and Storage Temperature Range	$T_J, T_{stg}$	-55 to 150	$^\circ C$
Thermal Resistance, Junction-to-Ambient *	$R_{\theta JA}$	57	$^\circ C/W$

\* The device mounted on 1in<sup>2</sup> FR4 board with 2 oz copper



**N-Channel 200-V (D-S) MOSFET**
**Electrical Characteristics** ( $T_A=25^\circ\text{C}$  Unless Otherwise Specified)

Symbol	Parameter	Limit	Min	Typ	Max	Unit
<b>STATIC</b>						
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	200			V
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	2		4	V
$I_{GSS}$	Gate Leakage Current	$V_{DS}=0V, V_{GS}=\pm 20V$			$\pm 100$	nA
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=200V, V_{GS}=0V$			1	$\mu A$
$R_{DS(ON)}$	Drain-Source On-Resistance <sup>a</sup>	$V_{GS}=10V, I_D=1.4A$		630	756	$m\Omega$
$V_{SD}$	Diode Forward Voltage	$I_S=1A, V_{GS}=0V$			1.2	V
<b>DYNAMIC</b>						
$Q_g$	Total Gate Charge	$V_{DS}=100V, V_{GS}=10V, I_D=1.4A$		14.3		nC
$Q_{gs}$	Gate-Source Charge			4.3		
$Q_{gd}$	Gate-Drain Charge			5		
$C_{iss}$	Input Capacitance	$V_{DS}=25V, V_{GS}=0V, f=1MHz$		583		pF
$C_{oss}$	Output Capacitance			27		
$C_{rss}$	Reverse Transfer Capacitance			6		
$t_{d(on)}$	Turn-On Delay Time	$V_{DS}=100V, R_L=71.4\Omega,$ $V_{GS}=10V, R_G=4.7\Omega$ $I_D=1.4A$		6.2		ns
$t_r$	Turn-On Rise Time			21.4		
$t_{d(off)}$	Turn-Off Delay Time			19.5		
$t_f$	Turn-Off Fall Time			27.3		







Notes: a. Pulse test: pulse width  $\leq 300\mu s$ , duty cycle  $\leq 2\%$ , Guaranteed by design, not subject to production testing.

b. Matsuki Electric/ Force mos reserves the right to improve product design, functions and reliability without notice.







**N-Channel 200-V (D-S) MOSFET**

**Typical Characteristics (T<sub>J</sub> = 25°C Noted)**




**N-Channel 200-V (D-S) MOSFET**

**Typical Characteristics (T<sub>J</sub> =25°C Noted)**



**SOT-223 Package Outline**



SYMBOL	COMMON					
	DIMENSIONS MILLIMETER			DIMENSIONS INCH		
	MIN.	MOM.	MAX.	MIN.	MOM.	MAX.
A	—	—	1.80	—	—	0.0709
A1	0.02	—	0.10	0.0008	—	0.0039
A2	1.50	1.60	1.70	0.0591	0.0630	0.0669
b	0.66	0.76	0.84	0.0260	0.0300	0.0330
b1	2.90	3.00	3.10	0.1142	0.1181	0.1220
C	0.23	0.30	0.35	0.0090	0.1181	0.1378
D	6.30	6.50	6.70	0.2480	0.2560	0.2638
E	6.70	7.00	7.30	0.2638	0.2760	0.2874
E1	3.30	3.50	3.70	0.1300	0.1378	0.1457
e	2.30 BSC			0.0906 BSC		
e1	4.60 BSC			0.1811 BSC		
L	0.75	—	—	0.0295	—	—
θ	0°	—	10°	0°	—	10°

