

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)MAX}$	I_D
60V	100m Ω @10V	3A
	120m Ω @4.5V	

Feature

- Advanced trench process technology
- High density cell design for ultra low on-resistance

Application


- Load Switch for Portable Devices
- DC/DC Converter

Package




SOT-23

Circuit diagram



Marking



Absolute maximum ratings (Ta=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V _{DS}	60	V
Gate-Source Voltage	V _{GS}	±20	V
Continuous Drain Current	I _D	3	A
Pulsed Drain Current	I _{DM}	12	A
Power Dissipation	P _D	1.2	W
Thermal Resistance from Junction to Ambient	R _{θJA}	105	°C/W
Junction Temperature	T _J	150	°C
Storage Temperature	T _{STG}	-55 ~ +150	°C

Electrical characteristics (T_A=25 °C, unless otherwise noted)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-source breakdown voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = 250μA	60			V
Zero gate voltage drain current	I _{DSS}	V _{DS} = 60V, V _{GS} = 0V			1	μA
Gate-body leakage current	I _{GSS}	V _{GS} = ±20V, V _{DS} = 0V			±100	nA
Gate threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	0.5		2	V
Drain-source on-resistance ¹⁾	R _{DS(on)}	V _{GS} = 10V, I _D = 3A		86	100	mΩ
		V _{GS} = 4.5V, I _D = 2A		92	120	
Dynamic characteristics²⁾						
Input Capacitance	C _{iss}	V _{DS} = 30V, V _{GS} = 0V, f = 1MHz		330		pF
Output Capacitance	C _{oss}			90		
Reverse Transfer Capacitance	C _{rss}			17		
Total Gate Charge	Q _g	V _{DS} = 30V, V _{GS} = 10V, ID = 3A		5.1		nC
Gate-Source Charge	Q _{gs}			1.3		
Gate-Drain Charge	Q _{gd}			1.7		
Turn-on delay time	t _{d(on)}	V _{DD} = 30V, V _{GS} = 10V I _D = 1.5A, R _{GEN} = 3Ω, R _L = 1Ω		13		nS
Turn-on rise time	t _r			51		
Turn-off delay time	t _{d(off)}			19		
Turn-off fall time	t _f			12		
Source-Drain Diode characteristics						
Diode Forward Current ¹⁾	I _S				3	A
Diode Forward voltage	V _{DS}	V _{GS} = 0V, I _S = 3A			1.2	V

Notes:

- 1) Pulse Test: Pulse Width < 300μs, Duty Cycle ≤ 2%.
2) Guaranteed by design, not subject to production testing.

Typical Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Capacitance Characteristics




Figure4. Gate Charge




Figure5. Drain-Source on Resistance







Figure6. Drain-Source on Resistance

SOT-23 Package Information


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP.		0.037 TYP.	
e1	1.800	2.000	0.071	0.079
L	0.550 REF.		0.022 REF.	
L1	0.300	0.500	0.012	0.020