







DC044A




SCHEMATIC

PIN

φ1.65

APPD

DC044A-2





SCHEMATIC

PIN

φ2

φ2.5

APPD



P.C.B LAYOUT

Specification:

1. Rating : DC 30V 0.5A.
2. Contact resistance: $\leq 70\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (250VDC).
4. Withstanding voltage: 250VAC.
5. Insertion and extraction force: 3N~30N.
6. life test: 5000cycles min.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 70^{\circ}\text{C}$.

B1	2020.7.01	Δ 新增视图及产品技术规格	GYW	
A5	2019.8.30	Δ 新增产品局部剖视图	GYW	
A4	2018.12.24	Δ 新增PCB板开孔尺寸标注	GYW	
A3	2018.12.07	Δ 修改“h”“i”尺寸公差为 ± 0.2	GYW	
A2	2018.11.12	Δ 修改BOM信息: 改用DC044B前盖无镀	GYW	
A1	2018.4.13	Δ 盖脚尺寸9.8改为10.0	GYW	
A0	2013.8.29	初版	LIU	
NO	DATE	REVISIONS	BY	APPD

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED	UP TO 5mm: ± 0.1 ABOVE 5mm: ± 0.2	ANGULAR $\pm 1^{\circ}$	TITLE: DC JACK	UNIT : MM	ROHS COMPLIANT	DWN	CHK'D	APPD	PRO.AGL:	REV :B1
7	DC044	PING	BRASS	1	Ni PLATED											
6	DC044A	COAT	SUS	1	Ni PLATED											
5	DC044B	COVER	SUS	1	WASH											
4	DC044	2#SPRING	SUS/PBS	1	Ag PLATED											
3	DC044	3#CURVE PIECE	BRASS	1	Ag PLATED											
2	DC044	4#FLAT PIECE	BRASS	1	Ag PLATED											
1	DC044A	CASE	PBT/PA9T	1	BLACK											



HAOYU(HONGKONG)LIMITED
皓宇(香港)有限公司