

## Product Summary

$V_{RRM}$	650 V
$I_F$ ( $T_c=155^\circ\text{C}$ )	10 A
$Q_c$	29 nC

## Features

- Extremely low reverse current
- No reverse recovery current
- Temperature independent switching
- Positive temperature coefficient on  $V_F$
- Excellent surge current capability
- Low capacitive charge

## Benefits

- Essentially no switching losses
- System efficiency improvement over Si diodes
- Increased power density
- Enabling higher switching frequency
- Reduction of heat sink requirements
- System cost savings due to smaller magnetics
- Reduced EMI

## Applications

- Switch mode power supplies (SMPS)
- Uninterruptible power supplies
- Motor drivers
- Power factor correction

## Package Pin Definitions

- Pin1 and backside - Cathode
- Pin2- Anode


## Package Parameters

Part Number	Marking	Package
B1D10065H	B1D10065H	TO-247-2

## Package: TO-247-2



## Electrical Connection



**Maximum Ratings ( $T_c=25^\circ\text{C}$  unless otherwise specified)**

Symbol	Parameter	Test conditions	Value	Unit
$V_{RRM}$	Repetitive peak reverse voltage		650	V
$V_{RSM}$	Non-repetitive peak reverse voltage		650	V
$I_F$	Continuous forward current	$T_c=25^\circ\text{C}$ $T_c=155^\circ\text{C}$	36 10	A
$I_{FSM}$	Non-repetitive forward surge current	$T_c=25^\circ\text{C}, t_p=10\text{ms}$ Half sine wave	75	A
$\int i^2 dt$	i <sup>2t</sup> value	$T_c=25^\circ\text{C}, t_p=10\text{ms}$	28.12	A <sup>2</sup> S
$P_{tot}$	Power dissipation	$T_c=25^\circ\text{C}$ $T_c=110^\circ\text{C}$	158 68	W
$T_j$	Operating junction temperature		-55~175	°C
$T_{stg}$	Storage temperature		-55~175	°C
	TO-247 mounting torque	M3 Screw	0.7	Nm

**Thermal Characteristics**





Symbol	Parameter	Value			Unit
		Min.	Typ.	Max.	
$R_{th(jc)}$	Thermal resistance from junction to case		0.946		K/W

**Electrical Characteristics**  
**Static Characteristics**

Symbol	Parameter	Test conditions	Value			Unit
			Min.	Typ.	Max.	
$V_{DC}$	DC blocking voltage	$T_j=25^\circ C$	650			V
$V_F$	Diode forward voltage	$I_F=10A T_j=25^\circ C$ $I_F=10A T_j=175^\circ C$		1.43 1.75		V
$I_R$	Reverse current	$V_R=650V T_j=25^\circ C$ $V_R=650V T_j=175^\circ C$		1 20		$\mu A$

**AC Characteristics**

Symbol	Parameter	Test conditions	Value			Unit
			Min.	Typ.	Max.	
$Q_C$	Total capacitive charge	$V_R=400V T_j=25^\circ C$ $Q_C=\int_0^{V_R} C(V)dV$		29		nC
C	Total capacitance	$V_R=1V f=1MHz$ $V_R=300V f=1MHz$ $V_R=600V f=1MHz$		457 49.7 49.3		pF
$E_C$	Capacitance stored energy	$V_R=400V$		4.5		$\mu J$

**Typical Performance**

**Figure 1** Typical forward characteristics

**Figure 2** Typical reverse current as function of reverse voltage

**Figure 3** Diode forward current as function of temperature, D=duty cycle

**Figure 4** Typical capacitance as function of reverse voltage,  $C=f(V_R)$ ;  $T_j=25^\circ\text{C}$ ;  $f=1 \text{ MHz}$

### Typical Performance




Figure 5    Typical reverse charge as function of reverse voltage




Figure 6    Power dissipation as function of case temperature




Figure 7    Capacitance stored energy





Figure 8    Max. transient thermal impedance,  $Z_{thjc} = f(t_p)$ , parameter:  $D = t_p / T$

**Package Dimensions**


SYMBOL	mm		
	MIN	NOM	MAX
A	4.80	5.00	5.20
A1	2.21	2.41	2.61
A2	1.85	2.00	2.15
b	1.11	1.21	1.36
b2	1.91	2.01	2.21
c	0.51	0.61	0.75
D	20.70	21.00	21.30
D1	16.25	16.55	16.85
D2	1.05	1.17	1.35
E	15.50	15.80	16.10
E1	13.00	13.30	13.60
E2	4.80	5.00	5.20
E3	2.30	2.50	2.70
e	10.88 BSC		
L	19.62	19.92	20.22
L1	-	-	4.30
φ P	3.40	3.60	3.80
φ P1	-	-	7.30
S	6.15 BSC		

## Revision History

Document Version	Date of Release	Description of Changes
Rev. 1.0	2019-10-08	Release of the datasheet.
Rev. 2.0	2020-07-06	Characteristics updated.
Rev. 2.1	2021-12-06	Characteristics updated.

**BASiC Semiconductor Ltd.**  
**Shenzhen, China**  
**© 2021 BASiC Semiconductor Ltd.**  
**All Rights Reserved.**

## Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest BASiC Semiconductor Office

## Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, BASiC semiconductor Ltd. hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.