

# ACH CONNECTOR 1.2 mm pitch/Disconnectable Crimp style connectors



This ACH connector is compact and low profile type, height 1.4 mm and width 4.3 mm, 1.2 mm pitch wire-to-board connector.

- Top entry but side feed type
- Connector for DC power supply
- Corresponding to sucking nozzle of pick and place machine

### Standards

- Recognized E60389
- Gertified LR20812

## Specifications

- Current rating: 1 to 3 circuits/ 2 A AC/DC (AWG #28) 4, 5 circuits/ 1.5 A AC/DC (AWG #28)
- Voltage rating: 50 V AC, DC
- Temperature range: -25°C to +85°C
  - (including temperature rise in applying electrical current)
- Contact resistance:Initial value/ 10 m $\Omega$  max. After environmental tests/ 20 m $\Omega$  max.
- Insulation resistance: 100 M $\Omega$  min.
- Withstanding voltage: 500 VAC/minute
   Applicable wire: Conductor size/ AWG #32 to #28 Insulation O.D./ 0.38 to 0.63 mm
- \* In using the products, refer to "Handling Precaution for Terminals and Connectors"described on our website (Technical documents of Product infomation page).
- \* Dimensional unit: mm
- \* RoHS2 Compliance
- \* Contact JST for details.









Note: 1. The above figure is the figure viewed from the connector mounting side.
2. Tolerances are non-cumulative: ± 0.05mm for all centers.
3. The dimensions above should serve as a guideline. Contact JST for details.

Contact



Model No.	Applicable wire range		Insulation O.D. (mm)	O'ty/rool	
	mm <sup>2</sup>	AWG#		Q ty/reer	
SACH-003G-P0.2	0.05 to 0.08	30 to 28	0.5 to 0.63	30,000	
SACH-003G-P0.2B	0.032 to 0.05	32 to 30	0.38 to 0.5	30,000	

Material and Finish

Copper alloy, nickel-undercoated, gold-plated

RoHS2 compliance

Contact	Crimping	Applicator			
	machine	Applicator	Crimp applicator with dies		
SACH-003G-P0.2 SACH-003G-P0.2B		MKS-L-10-3	APLMK SACH003-02		
SACH-003G-P0.2B	AP-KZN	MKS-L-10-3	APLMK SACH003-02		

Note: Contact JST for fully automatic crimping applicator.



# ACH CONNECTOR

### Housing



No. of circuits	Model No.	Dimensi	Dimensions (mm)	
	WOULEI NO.	A	В	bag
1	ACHR-01V-A-S	-	1.6	2,000
2	ACHR-02V-S	1.2	2.6	1,000
3	ACHR-03V-S	2.4	3.8	1,000
4	ACHR-04V-A-S	3.6	5.0	1,000
5	ACHR-05V-A-S	4.8	6.2	1,000

#### Material and Finish

Thermoplastic resin, UL94V-0, natural (white)

RoHS2 compliance

### Header



No. of circuits	Model No.	Dimensio	Q'ty∕	
	Model No.	А	В	reel
1	BM01B-ACHSS-A-GAN-ETF	—	3.2	4,500
2	BM02B-ACHSS-GAN-ETF	1.2	4.2	4,500
3	BM03B-ACHSS-GAN-ETF	2.4	5.4	4,500
4	BM04B-ACHSS-A-GAN-ETF	3.6	6.6	4,500
5	BM05B-ACHSS-A-GAN-ETF	4.8	7.8	4,500

#### Material and Finish

Contact: Copper alloy, nickel-undercoated, gold-plated (nickel-stripe) Housing: Heat resisting resin, UL94V-0, natural (ivory) Solder tab: Copper alloy, copper-undercoated, tin-plated

RoHS2 compliance This product displays (LF) (SN) on a label.

# ACH CONNECTOR

### Model number allocation

#### Contact



#### Header

		B-ACH		<u> </u>		
Shape of assembled product: BM···SMT Top entry type						
No. of circuits: 1 to 5						
Part name: Header						
Series name						
Color: S…Natural (Ivoly), K…	Black		-			
Indication of clinch: S···Straig	nt pin					
Type: None····2, 3-circuit produ	ict, A··	·1, 4, 5-cir	cuit p	product		
Surface finish: GAN···Nickel-u	ndercoa	ted gold-p	lated	(nickel	stripe)	
Packaging style: ETF···Embos	end-tan	ng				-

#### Housing

