



General Features

- $V_{DS} = -60V, I_D = -1.6A$
- $R_{DS(ON)} < 200m\Omega @ V_{GS} = -10V$
- $R_{DS(ON)} < 240m\Omega @ V_{GS} = -4.5V$

Application


- Load/Power Switching
- Interfacing Switching
- Logic Level Shift

Package and Pin Configuration

SOT-23



Circuit diagram



Absolute Maximum Ratings ($T_C = 25^\circ C$ unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V_{DS}	-60	V
Gate-Source Voltage	V_{GS}	± 20	V
Drain Current-Continuous	I_D	-1.6	A
Pulsed Drain Current ^(Note 1)	I_{DM}	-8	A
Maximum Power Dissipation	P_D	1.5	W
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55 To 150	°C

Thermal Characteristic

Thermal Resistance, Junction-to-Ambient ^(Note 2)	$R_{\theta JA}$	83.3	°C/W
---	-----------------	------	------



Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Off Characteristics						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=-250\mu\text{A}$	-60	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}}=-60\text{V}, V_{\text{GS}}=0\text{V}$	-	-	-1	μA
Parameter	Symbol	Condition	Min	Typ	Max	Unit
Gate-Body Leakage Current	I_{GSS}	$V_{\text{GS}}=\pm 20\text{V}, V_{\text{DS}}=0\text{V}$	-	-	± 100	nA
On Characteristics <small>(Note 3)</small>						
Gate Threshold Voltage	$V_{\text{GS(th)}}$	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=-250\mu\text{A}$	-1.4	-2.0	-2.6	V
Drain-Source On-State Resistance	$R_{\text{DS(ON)}}$	$V_{\text{GS}}=-10\text{V}, I_{\text{D}}=-1.5\text{A}$	-	150	200	$\text{m}\Omega$
		$V_{\text{GS}}=-4.5\text{V}, I_{\text{D}}=-1.5\text{A}$	-	190	240	$\text{m}\Omega$
Forward Transconductance	g_{FS}	$V_{\text{DS}}=-5\text{V}, I_{\text{D}}=-1.5\text{A}$	-	3	-	S
Dynamic Characteristics <small>(Note 4)</small>						
Input Capacitance	C_{iss}	$V_{\text{DS}}=-30\text{V}, V_{\text{GS}}=0\text{V}, F=1.0\text{MHz}$	-	444.2	-	PF
Output Capacitance	C_{oss}		-	19.6	-	PF
Reverse Transfer Capacitance	C_{rss}		-	17.9	-	PF
Switching Characteristics <small>(Note 4)</small>						
Turn-on Delay Time	$t_{\text{d(on)}}$	$V_{\text{DD}}=-30\text{V}, I_{\text{D}}=-1.5\text{A}, V_{\text{GS}}=-10\text{V}, R_{\text{G}}=3\Omega$	-	40	-	nS
Turn-on Rise Time	t_{r}		-	35	-	nS
Turn-Off Delay Time	$t_{\text{d(off)}}$		-	15	-	nS
Turn-Off Fall Time	t_{f}		-	10	-	nS
Total Gate Charge	Q_{g}	$V_{\text{DS}}=-30, I_{\text{D}}=-1.5\text{A}, V_{\text{GS}}=-10\text{V}$	-	11.3	-	nC
Gate-Source Charge	Q_{gs}		-	2.7	-	nC
Gate-Drain Charge	Q_{gd}		-	1.6	-	nC
Drain-Source Diode Characteristics						
Diode Forward Voltage <small>(Note 3)</small>	V_{SD}	$V_{\text{GS}}=0\text{V}, I_{\text{S}}=-1.5\text{A}$	-		-1.2	V
Diode Forward Current <small>(Note 2)</small>	I_{S}		-	-	-1.6	A
Reverse Recovery Time	t_{rr}	$T_J = 25^\circ\text{C}, I_F = -1.5\text{A}$ $di/dt = -100\text{A}/\mu\text{s}$ <small>(Note 3)</small>	-	25		nS
Reverse Recovery Charge	Q_{rr}		-	31		nC



Typical Electrical and Thermal Characteristics (Curves)




Figure 1 Output Characteristics




Figure 4 Rdson-Junction Temperature




Figure 2 Transfer Characteristics




Figure 5 Gate Charge




Figure 3 Rdson-Drain Current




Figure 6 Source-Drain Diode Forward




Figure 7 Capacitance vs Vds




Figure 9 BV_{DSS} vs Junction Temperature




Figure 8 Safe Operation Area




Figure 10 I_D Current De-rating





Figure 11 Normalized Maximum Transient Thermal Impedance

SOT-23 Package Information

Symbol	Dimensions in Millimeters	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
θ	0°	8°