




P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-11-005030	24MAR2011	RK	HMR
	E	REVISED PER ECR-20-003937	16MAR2020	T.S	E.I



RECOMEND PC BOARD HOLE PATTERN
PC BOARD THICKNESS: 1.6 ± 0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

- 1. MATERIAL: HOUSING : GLASS FILED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- 2. FINISH (CONTACT AREA): $0.38 \mu\text{m}$ MIN GOLD PLATING OVER Ni PLATING.
- 3. FINISH (CONTACT AREA): $0.76 \mu\text{m}$ MIN GOLD PLATING OVER Ni PLATING.
- 4. FINISH (CONTACT AREA): $2.0 \mu\text{m}$ MIN TIN PLATED OVER NICKEL.
- 5. NOTE DELETED
- 6. FINISH (RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL.
- 7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

Y			2-178318-5	OBSOLETE
			2-178318-3	
			2-178318-2	
X			1-178318-5	
			1-178318-3	
			1-178318-2	
KEYING	FINISH	PART NO		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. SHIMOYASU 16MAR2020	TE Connectivity	
		CHK E. IKEMATSU 16MAR2020		
DIMENSIONS: mm		APVD E. IKEMATSU 16MAR2020	NAME IOPOSN VERTICAL HEADER ASSEMBLY DYNAMIC D3100S	
		PRODUCT SPEC 108-5349	SIZE A3	
		APPLICATION SPEC -	CAGE CODE 00779	
MATERIAL -		WEIGHT -	DRAWING NO C-178318	
FINISH -		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE 2:1		SHEET 1 OF 1
				REV E