







PIN ASSIGNMENT:

PIN NO	A1&B12	A4&B9	A5	B5	A9&B4	A12&B1
SIGNAL NAME	GND	VBUS	CC1	CC2	VBUS	GND
PCB PAD NO.	C1	C2	C3	C4	C5	C6



NOTES:

SPECIFICATION:

- 1.CURRENT RATING: 3.0A MAX
- 2.VOLTAGE: 100 VAC
- 3.TEMPERATURE RANGE: -30°C~+85°C
- 4.CONTACT RESISTANCE: 40 MILLIONHM MAX
- 5.INSULATION RESISTANCE: 100 MEGOHMS MIN
- 6.INSERTION FORCE: 5N~20N
- 7.UNMATING FORCE: 8N~20N
- 8.DURABILITY: 10000 CYCLES
- 9.WATER PROOFNESS:THISPRODUCTIS BASED ON IPX7.


端子 1A
中隔片 1A
外壳 1B
屏蔽壳 1A



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD

品名 (ITEM NO)	TYPE C 6P 沉板防水母座 (外壳4脚插板, 端子SMT)
料号 (PART NO)	YTC-WP6-45
图号 (DWG NO)	YTC-021

REV. (版本号)	DESCRIPTION (变更说明)	DATE (日期)	APPD (核准)
A1	新订图面	2020. 11. 13	LUO



加防水圈示意图




TABLE:

NO	PART	Q'TY	Material
1	SHELL	1	STAINLESS STEEL,NI PLATED
2	CONTACT	6	COPPER STEEL,TIN/Au/NI PLATED
3	MID PLATE	1	STAINLESS STEEL,NO PLATING
4	1MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
5	2MD HOUSING	1	HIGH TEMPERATURE RESISTANT PLASTIC BLACK UL94 V-0
6	SHIELDING PLATE	1	STAINLESS STEEL,NI PLATED

页码 (SHEET)	1/1	单位(UNIT) : MM
版本 (REV)	A1	比例(SCALE) 1:1
日期 (DATE)	2020. 11. 13	未注公差 TOLERANCE UNSPECIFIED
设计 (DESIGN)	LUO JIE	X.X ±0.30
审核 (CHECKED)	ROGER LI	X.XX ±0.20
核准 (APPROVED)	ROC ZHAO	X.XXX ±0.10
		X° ±5°
		X.X° ±2°